

6

5





4

3

2

1

MATERIAL NUMBER	OLD PART NUMBER
120099-0001	BR5L30



WIRING DIAGRAM

VOLTAGE RATING	250 VAC/VDC
AMPERAGE RATING	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 80°C

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACT	COPPER ALLOY	GOLD OVER NICKEL
3	GASKET	NITRILE	BLACK
4	RECEPTACLE SHELL	BRASS	NICKEL PLATED
5	LOCKWASHER	STEEL	ZINC PLATED
6	LOCKNUT	BRASS	NICKEL PLATED

RLSD DRAWING	EC NO: WNA2010-0139	8/27/09	DRWN: BWOODMAN	CHKD: JIM	APPR: JFMURPHY	2009/08/31
A						

QUALITY SYMBOLS
$\nabla = 0$
$\nabla / \sqrt{} = 0$

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±----	±---
3 PLACES	±----	±---
2 PLACES	±----	±.01
1 PLACE	±0.3	±---

ANGULAR ±---°
DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY	DATE
BW	2009/08/27
CHECKED BY	DATE
LH	2009/08/27
APPROVED BY	DATE
JFMURPHY	2009/08/28
MATERIAL NO.	
SEE CHART	
SIZE	A

SCALE
---DESIGN UNITS
----

TITLE	
MICRO-CHANGE BULKHEAD 5P FEMALE/MALE PROFIBUS M16 MOUNTING THREADS	
MOLEX INCORPORATED	
DOCUMENT NO.	SHEET NO.
SD-120099-003	1 OF 1

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

6

5

4

3

2

1