

ADDA USA

DC FAN SPECIFICATIONS

Frame Dimensions (mm)	Model Part Number	Bearing Type	Volts (V)	Current (A)	Power (W)	Speed (RPM)	Air Flow (CFM)	Pressure (Inches)	Noise (dB/A)	Weight (g)	Features Available	Safety Approvals	Units Per Box	Box Wt. (lbs.)
40 X 40 X 6	AD0405LX-KC0	HYPRO	5	0.11	0.55	4500	3.6	0.061	22.4	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LX-KC3	HYPRO	5	0.08	0.40	4500	4.6	0.068	27.1	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-K90	HYPRO	5	0.09	0.45	5500	5.2	0.064	23.8	9	0,6	UL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC0	HYPRO	5	0.20	1.00	5500	4.6	0.093	28.6	9	0,3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MX-KC3(Y)	HYPRO	5	0.11	0.55	5500	4.6	0.093	28.6	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-K90	HYPRO	5	0.12	0.60	6300	6.0	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC0	HYPRO	5	0.23	1.15	6000	5.0	0.110	31.2	9	0	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HX-KC3	HYPRO	5	0.13	0.65	6000	5.0	0.110	31.2	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405LB-K90(S)	1B,1S	5	0.05	0.25	4800	4.5	0.051	19.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-K90(S)	1B,1S	5	0.09	0.45	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MB-KC3	BALL	5	0.11	0.55	5800	4.9	0.102	30.0	9	3	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405HB-K90(S)	1B,1S	5	0.12	0.60	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0405MS-K90	S	5	0.09	0.45	5500	5.2	0.064	23.8	9	0	CE	400	13.20
40 X 40 X 6	AD0412LX-K90	HYPRO	12	0.06	0.72	4500	4.4	0.049	20.9	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MX-K90	HYPRO	12	0.06	0.72	5500	5.2	0.064	23.8	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HX-K90	HYPRO	12	0.08	0.96	6300	5.9	0.079	27.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412LB-K90(S)	1B,1S	12	0.06	0.72	4800	4.7	0.049	21.6	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412MB-K90(S)	1B,1S	12	0.06	0.72	5800	5.5	0.067	25.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 6	AD0412HB-K90(S)	1B,1S	12	0.08	0.96	6600	6.0	0.090	30.0	9	0,6	UL,CUL,TUV,CE	400	13.20
40 X 40 X 8	AD0405LX-J90	HYPRO	5	0.12	0.60	4100	5.1	0.058	20.0	5	0	CE		
40 X 40 X 8	AD0405MX-J90	HYPRO	5	0.16	0.80	5500	6.3	0.094	28.7	5	0	CE		
40 X 40 X 8	AD0405MX-J93	HYPRO	5	0.15	0.75	5500	6.8	0.098	29.0	5	3	CE		
40 X 40 X 8	AD0405HX-J91	HYPRO	5	0.23	1.15	6000	7.5	0.110	31.0	5	1,3	CE		
40 X 40 X 8	AD0405MB-J90	BALL	5	0.20	1.00	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 8	AD0412MX-J90	HYPRO	12	0.13	1.56	5000	6.1	0.089	26.0	5	0	CE		
40 X 40 X 9	AD0405HX-RA3	HYPRO	5	0.25	1.25	6000	3.1	0.334	40.3	5	3	CE		
40 X 40 X 10	AD0405DX-G70	HYPRO	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LX-G70	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LX-G76	HYPRO	5	0.08	0.40	4200	4.7	0.060	14.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405MX-G70	HYPRO	5	0.11	0.55	4800	5.7	0.780	19.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MX-G7	HYPRO	5	0.11	0.55	4800	5.7	0.078	20.0	24	6	UL,CUL,CE	700	
40 X 40 X 10	AD0405HX-G70	HYPRO	5	0.19	0.95	6000	6.7	0.100	25.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405DB-G70	BALL	5	0.07	0.35	3300	3.8	0.044	14.5	24	0	CE	700	
40 X 40 X 10	AD0405LB-G70	BALL	5	0.08	0.40	4600	5.0	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G70	BALL	5	0.11	0.55	4800	5.7	0.078	20.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G72	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	2	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MB-G73	BALL	5	0.15	0.75	4800	5.7	0.078	20.0	24	3	CE	700	
40 X 40 X 10	AD0405MB-G76	BALL	5	0.11	0.55	5000	6.0	0.080	20.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G70	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	0	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405HB-G72	BALL	5	0.25	1.25	6000	6.7	0.100	25.0	24	2	CE	700	
40 X 40 X 10	AD0405HB-G76	BALL	5	0.19	0.95	6000	6.8	0.100	25.0	24	6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405LS-G70	S	5	0.08	0.40	4200	4.7	0.060	14.0	24	0,6	UL,CUL,TUV,CE	700	
40 X 40 X 10	AD0405MS-G70	S	5	0.11	0.55	4800	5.7	0.078	20.0	24	0,2,6	UL,CUL,TUV,CE	700	

NOTE B=Ball S=Sleeve X= Hypro AT= Terminals AW= Wires

ALL RIGHTS RESERVED