





Terminal Blocks

158-P02EK500A2-E, 158-P02EK500A3-E

KOBICONN

Terminal Blocks



Dimensions: mm

ELECTRICAL SPECIFICATIONS

Rating:	300V 20A
Pitch:	5mm
Insulation	AC 1500 V/min
Withstands Voltage:	
Insulation Resistance	4A
Temp Range	-40°C~+105°C
Screw Torque Value	4Kgf-cm
Wire Gauge :	12-24 AWG

MECHANICAL SPECIFICATIONS

Part	Material
1 - Housing:	PA66(V2) - Green
2 - Screw:	Steel - M2.5/Zn Plated
3 - Wire Cage:	Steel - M2.5/Zn Plated
4 - Solder Pin:	Copper - Tin Plated

Date Last Revised: 10-18-06

Available from Mouser Electronics
1-800-346-6873
www.mouser.com

KC-301077

158-P02EK500A2-E, 158-P02EK500A3-E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Kobiconn:](#)

[158-P02EK500A3-E](#) [158-P02EK500A2-E](#)