





LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	3000pF MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE -55°C TO 125°C	115VAC @ 400Hz 500VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
10	12
30	20
100	45
300	60
500	--
1GHz	60
10GHz	60



MARKING:

PART: S011 (FAIRVIEW)
 S011M (MEXICO)

(MARKING MUST BE CLEARLY LEGIBLE
 WITH NO MARKING VOIDS)

BAG:
 51-719-011
 DATE CODE
 QTY./BAG (100 MAX.)

REV. NO.	68	67	66	65	64	63	62	61
CHANGE NOTICE	CN 35419-ENG	CN 16164-CPD	CN 13776-CPD	CN 212860	CN 201356	CN 197374	CN 193211	CN 184956 REDRAWN
TOLERANCES UNLESS OTHERWISE SPECIFIED	Fractions ± 1/64							
	Dec. .xx±							
	Dec. .xxx±.010							
	Angles ±0° 30'							
CODE IDENT. NO.	DLSP2							

 FAIRVIEW PENNSYLVANIA SPECTRUM CONTROL INC.	
Dwn. KAUFFMAN	Description Pi
Date 6-12-07	RESIN SEAL FILTER
Engr. SACKETT	51-719-011
Scale NONE	

