


2 mm Size Detector Switches, 2ND

Japan

Type: **ESE22**

Easy-to-use “through operation,” operable in two directions at right angles



■ Features

- Highly-operable drive type (horizontally, vertically and diagonally)
- Available for reflow soldering
- Lightweight

■ Recommended Applications

- Audio Systems (MD/CD Players)
- Detection of mechanical position mode for CD-ROM Drives, etc.

■ Explanation of Part Numbers

1	2	3	4	5	6	7	8	9
E	S	E	2	2				
Product Code			Type		Style		Design No.	

■ Major Specifications

Rating	50 μ A 3 Vdc to 10 mA 5 Vdc (Resistive load)	
Operating Force	300 mN max.	
Mounting Height	1.9 mm	
Poles and Throws	1-pole 1-throw	
Minimum Quantity/Packing Unit	Bulk	500 pcs. (Vinyl Bag)
	Embossed	4000 pcs. (Reel Pack)
Quantity/Carton	Bulk	10000 pcs.
	Embossed	24000 pcs.


■ Dimensions in mm (not to scale)

[illegible]

Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use. Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.

Design, Specifications are subject to change without notice. Ask factory for technical specifications before purchase and/or use. Whenever a doubt about safety arises from this product, please inform us immediately for technical consultation without fail.

■ Dimensions in mm (not to scale)



■ Packaging Specifications

Standard Reel Dimensions in mm (not to scale)

