







RECOMMEND P.C.B. LAYOUT



CIRCUIT: SPST
CONTACT CONFIGURATION

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: 0.0=±0.4
0.00=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA @12V DC
5. TRAVEL: 0.25±0.1mm
6. OPERATING FORCE: 130±50gf
7. CONTACT RESISTANCE: 100m ohm max.
8. MECHANICAL/ELECTRICAL LIFE: 40,000 CYCLES
9. PACKAGE: BULK, 1,000 PER BAG
10. 2002/95/EC (ROHS) COMPLIANT

REV.		ECN No.	DESCRIPTION	DATE	CHKD
B		16628	UPDATED NOTES	11/9/06	TN
A		10584	RELEASED FOR PRODUCTION	3/28/00	MM
REV.		ECN No.	DESCRIPTION	DATE	CHKD

THE INFORMATION CONTAINED IN THIS DOCUMENT
IS PROPRIETARY TO E-SWITCH AND IS
NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE		DATE		DR		DWG		REV	
TL1107AF130BQ		11/9/2006		TN		P010380		B	
SCALE		5:1							