



707 8249
↓
8407

SANDVIK BELZER

**Double hexagon
Metric**

DIN 3214/ISO 2725.

1/4" ● 6.3 DIN 3120/ISO 1174.

Finish: nickel and chrome-plated, fine-polished.



Material: VANADIUM-EXTRA.

High performance sockets, thin-walled, Dynamic-Drive-Profile.

Product code	EAN code 731415+		Dim. mm	L mm	D ₁ mm	D ₂ mm	T mm	
A6700DM-5.5	1821678	5	5,5	23	8,4	11,2	6	10
A6700DM-6	1821685	5	6	23	9	11,2	6,5	10
A6700DM-7	1821692	5	7	23	10,3	11,2	7,5	10
A6700DM-8	1821708	5	8	23	11,5	11,2	8,5	11
A6700DM-9	1821715	5	9	23	12,8	11,2	9,5	14
A6700DM-10	1821722	5	10	23	14	12	10,5	15
A6700DM-11	1821739	5	11	23	15,3	13	10,5	18
A6700DM-12	1821746	5	12	25	16,5	14	11,5	20
A6700DM-13	1821753	5	13	25	17,8	15	11,5	25
A6700DM-14	1821760	5	14	25	19	16	12,5	27



A6700DM



Product code	EAN code 731415+		Dim. inch	L mm	D ₁ mm	D ₂ mm	T mm	
A6700DZ-3/16	1751029	5	3/16	23	7,5	11,2	5,5	10
A6700DZ-7/32	1751296	5	7/32	23	8,5	11,2	6	10
A6700DZ-1/4	1751371	5	1/4	23	9,5	11,2	6,5	10
A6700DZ-9/32	1751456	5	9/32	23	10,5	11,2	7,5	10
A6700DZ-5/16	1751531	5	5/16	23	11,5	11,2	8,5	10
A6700DZ-11/32	1819842	5	11/32	23	12,5	11,2	9,5	10
A6700DZ-3/8	1751616	5	3/8	23	13,5	11,2	10,5	16
A6700DZ-7/16	1819859	5	7/16	23	15,4	13	10,5	25
A6700DZ-1/2	1751883	5	1/2	25	17,4	15	11,5	27
A6700DZ-9/16	1751968	5	9/16	25	19,4	16,5	12,5	28




Inch

A6700DZ

Dynamic-Drive-Profile

Low surface pressure due to large force-applying surfaces



No notching sensitivity

These sockets are suitable for all nuts and bolts used in the aerospace industry.

DIN	65546, 65438, 65443,
LN	29520, 29542, 29550, 29551, 29769, 29901 - 29903, 29934, 29955,
	65056, 65101 - 65106, 65416 - 65418, 29529, 29894, 29919, 65414,
VLN	29953,
EN	2907, 3013.