




(2,54 mm) .100"

SLW, CES SERIES

LOW PROFILE SOCKET STRIPS

SPECIFICATIONS

For complete specifications see www.samtec.com?SLW or www.samtec.com?CES

Insulator Material:

Black G.F. Polyester

Contact Material:

Phosphor Bronze

Plating: Au or Sn over 50µ" (1,27 µm) Ni

SLW Current Rating

(SLW/TSW):

5.2 A per pin

(1 pin powered per row)

CES Current Rating

(TSW/CES):

5.5 A per pin

(1 pin powered per row)

Voltage Rating:

SLW: 406 VAC

CES: 400 VAC

Operating Temp Range:

-55°C to +125°C with Gold

-55°C to +105°C with Tin

Contact Resistance:

10 mΩ

Insertion Depth:

SLW: (2,16 mm) .085" to (2,92 mm) .115"

CES: (2,62 mm) .103" to (4,06 mm) .160"

Insertion Force:

SLW: (Single contact only)

(3,34 N) 12 oz. avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only)

(2,22 N) 8 oz. avg.

(0,64 mm) .025" SQ pin

Withdrawal Force:

SLW: (Single contact only)

(1,67 N) 6 oz. avg.

(0,64 mm) .025" SQ pin

CES: (Single contact only)

(1,11 N) 4 oz. avg.

(0,64 mm) .025" SQ pin

RoHS Compliant:

Yes

Lead-Free Solderable:

Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



FILE NO. E111594

FILE NO. 090071_0_000 (CES ONLY)

ALSO AVAILABLE (MOQ Required)

- Other platings
- Contact Samtec.

Note: Some lengths, styles and options are non-standard, non-returnable.

SLW

1

NO. PINS PER ROW

01


PLATING OPTION

ROW OPTION

Mates with:

TLW, TSW, MTLW, MTSW, HW, EW, ZW, HTSW, HMTSW, TSM

01 thru 50



-F

= Gold flash on contact, Matte Tin on tail

-L

= 10µ" (0,25 µm) Gold on contact, Matte Tin on tail

-G

= 20µ" (0,51 µm) Gold on contact, Gold flash on balance

-T

= Matte Tin

-S
= Single Row

-D
= Double Row

CES

1

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION


ROW OPTION

RA OPTION

Mates with:

TLW, TSW, MTLW, MTSW, HW, EW, ZW, DW, HTSW, PHT, HMTSW

01 thru 50



-01

= (3,25 mm) .128 "A" Dim.

-02

= (5,66 mm) .223 "A" Dim.

-L

= 10µ" (0,25 µm) Gold contact, Matte Tin on tail

-T

= Matte Tin

-S

= Single Row

-D

= Double Row

-RA

= Right Angle version

Style -02 only
Single Row only

