


NO. OF CKTS.	SOCKET DIMENSIONS			
	"A"		"B"	
	IN.	MM	IN.	MM
6	0.48	12.2	0.20	5.1
10	0.68	17.3	0.40	10.2
14	0.88	22.4	0.60	15.2
16	0.98	24.9	0.70	17.8
20	1.18	30.0	0.90	22.9
26	1.48	37.6	1.20	30.5
30	1.68	42.8	1.40	35.6
34	1.88	47.8	1.60	40.6
40	2.18	55.4	1.90	48.3
50	2.68	68.1	2.40	61.0
60	3.18	80.8	2.90	73.7
64	3.38	85.9	3.10	78.7

U.L. RECOGNIZED: FILE E73711

- NOTES;
1. HOUSING MATERIAL: GF PBT 94V0 LIGHT GRAY
 2. CONTACT MATERIAL: PHOS BRONZE W/ GOLD OR PALLADIUM NICKEL WITH GOLD FLASH IN MATING AREA AND MATTE TIN PLATING OVER NICKEL ON IDC TAILS. BRIGHT TIN OVER NI OVERALL FOR -1- PART.
 3. ALL DIMENSIONS SHOWN IN INCHES AND mm.
 4. CONSULT FACTORY FOR NUMBER AND LOCATION OF AUXILIARY CODING SLOTS.

SOCKET PART NUMBERING SYSTEM



										PANCON CONNECTORS www.pancon.de / GERMANY www.panconconnectors.com / USA	Bolingbrook, Illinois
										LAT-CON™ 050 SERIES SOCKET CONNECTOR	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .005(.13) (.XX) ± .02(.5) ANGLES ±	UNLESS OTHERWISE SPEC- IFIED, ALL DIMENSIONS ARE GIVEN IN INCHES. THIRD ANGLE PROJECTION.
										DRAWN BY DDU	SCALE NONE
19				SEE SHEET 1						DATE 4-17-86	DRAWING NO. KA-10239
REV	DATE	BY	CHK	DESCRIPTION	CN - R	CUST	SUP			SEE NOTES	SHT 2 OF 2
										CHK'D WJH	DWG. A SIZE