










Axiall fter Axial Fans Ventilateurs Axial





L
D301L/M



L
D303L/M




M
D304L/M




D301, D303, D304

12 VDC



D301, D303, D304

24 VDC



D300	mm	inch
D1	30	1.181
D2	27.5	1.083
L1	36	1.417
L2	18	0.709
L3	3	0.118
B	2.6	0.102
Q1	34	1.338
Q2	28	1.102
R	3	0.118



Types -1  -3  -4 			D301/D303/D304		
	U _N	V	12	24	
	U	V	9...15	18...30	
	I _N	mA	48	22	
	I _{max}	mA	60	27	
	I _{block}	A	0.9	0.45	
	P _N	W	0.58	0.53	
	n	min ⁻¹	13 750	13 750	
	$\dot{V}$	l/min; CFM	146/5.16	146/5.16	
	p	Pa	130	130	
	LpA	dB(A)	42	42	
	MTTF	hr	5000		
	T	°C/F	-20...+65 / -5...+150		
	m	g/oz.	32/1.13		
	L/M	mm/inch	210/8.268		
	PPO	UL-94V-1	o.k.		
	Aluminium		-		
			o.k.		
			-		
			option		
			-		
			-		
			-		

