


LTR	REV.	DESCRIPTION	DATE



1.CABLE: C1: UL-2725 [#28(7/0.127 T.C)×1P INS:Foam-PE+D.W(7/0.127 T.C)+AL/MY
+Hot-melt-Mylar]×2C+#28(7/0.127 T.C)×1P INS:Polyolefin
+#24(7/0.203 T.C)×2C INS:Polyolefin+AL/MY+B.D(85%)
PVC JACKET; OD:5.5±0.15mm COLOR:WHITE(NK-W27) REV 3.0.
C2: UL-2725 #28(7/0.127 T.C)×2C+AL/MY+SPIRAL PVC JACKET;
OD:2.8±0.15mm COLOR:WHITE(NK-W27)

2.CONNECTOR: P1&P2:USB 3.0 A TYPE MALE 9PIN CONTACT:30u",SHELL:NI-PLATED.
P3:USB 3.0 MICRO B TYPE MALE CONTACT:30u",SHELL:NI-PLATED.

3.HOOD: P1&P2:MOLDED TYPE,PVC 45P,COLOR:WHITE(NK-W27).
P3:MOLDED TYPE,PVC 45P,COLOR:RED(NK-R01).

4.ELECTRICAL TEST:
(1)100% OPEN SHORT & MIS WIRE TEST .
(2)CONTACT RESISTANCE 3 ohm Max .
(3)INSULATION RESISTANCE 10M ohm Min .

5.PACKING:EACH PC / POLYBAG+SMALL HEADER CARD+BAR CODE LABEL
10 PCS / INNER CARTON
4 PCS INNER CARTON / MASTER CARTON(SIZE: 460×280×245mm)

Tolerance Inch M/M			Rotronic Co., LTD.					
.X	.015	.30						
.XX	.010	.10	ROLINE USB 3.0 Y-Cable, 2xAM - 1xMicro BM					
.XXX	.005	.05						
Draw FANNIE 06/23/11'			Item No.: 19.08.1008					
Check								
Engr			Scale	NONE	Units	m/m	Third Angle Projection	
			Dwg No.		170-0017	REV: A		Sheet 1/1