




SINGLE POLE 2MM CONNECTORS

These robust versatile connectors are supplied either with resilient pins or resilient sockets so that the type suitable to individual application can be chosen.

L1727 – Single pole plug, free end entry

L1727A/J/ - Single pole plug, free, end entry, resilient. Beryllium copper spring clips ensure high performance

CURRENT RATING:	10A for temperature rise <10°C
CONTACT RESISTANCE:	≤ 3 milliohms
TEMPERATURE RANGE (AMBIENT):	-40°C to +50°C (+65°C at 5 A max)
INSERTION FORCE (MAXIMUM):	15.7 N 3-5 bit
WIRE SIZE OVERALL (MAXIMUM):	3.1mm
WIRE SIZE CONDUCTOR (MAXIMUM):	1.8mm
CONNECTION:	Crimp or solder
INSULANT:	PVC
COLOURS:	
	L1727: Black or red
	L1727A/J/: Black, green, blue, red, white and yellow
WEIGHT (AVERAGE):	0.92g
FINISH:	Silver plated brass



BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
 Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>

BLP reserve the right to change without prior notice the information contained within this leaflet

BLP Components Ltd., Exning Road, Newmarket, Suffolk, CB8 0AX, England
Tel: +44 (0)1638 665161 Fax: +44 (0)1638 660718 email: sales@blpcomp.com <http://www.blpcomp.com>