

Products

Product On-Line Catalog

[Product Search](#)

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet

- PDF-G.75X2BL6 Pr

- Part Drawings

- PDF-Type G 1x2 W ..

- DWG-Type G 1x2 W ..

- DXF-Type G 1x2 W ..

How to Buy

- Bill of Material

- Favorite Products List

- Locate Distributor


[Home](#) > [Product On-Line Catalog](#) > [Product Search](#) >

Current refinements (click  to remove) Search Tips 

[Part Number](#) > **G1X2BL6**

Your search criteria matched only one product, shown below

G1X2BL6



Choose from 22 sizes of Panduit Type G Wiring Duct from 0.75" x 2.0" up to 4.0" x 5.0" in color. Used for general purpose control panel wiring and to route and protect wiring in communication closets. The non-slip cover conceals all wiring and is easy to install. The duct cover forms a flush sidewall providing increased capacity and improved aesthetics.

Specifications

• Base and covers sold separately

- Made of lead-free PVC
- UL Recognized continuous use temperature: 122 °F (50°C)
- UL94 Flammability Rating of V-0
- Conforms with NFPA 79-2002 section 14.3.1 requirement for flame retardant material
- Provided with mounting holes

Features and Benefits

- Wide finger/slot design provides greater sidewall rigidity and can be used with a wide range of wire bundle sizes

- Panduit exclusive rounded edges protect hands and wiring/cabling from abrasion
- Non-slip cover stays in place during shipment, vibration and when in vertical orientation, eliminating rework
- Flush cover design holds 10-12% more wires than traditional duct designs
- Double scoreline allows quick modification for larger cabling bundles saving installation time leading to a lower installed cost
- Specially formulated lead-free material eliminates health concerns associated with PVC that contains lead
- Restricted slot design retains wire in slot for fast, easy wire installation or removal

Base and cover sold separately.

■ Part Number	G1X2BL6
■ RoHS Compliance Status	Compliant
■ Part Description	Wide finger, slotted wiring duct. Base and covers sold separately.
■ Product Type	Type G Wide Slot Wiring Duct
■ Material	Lead-Free PVC
■ Color	Black
■ CSA Certified	Yes
■ UL Recognized (File No. E147128)	Yes
■ Height (In.)	2.12
■ Height (mm)	53.8
■ Length (ft.)	6
■ Length (mm)	1828.8
■ Width (In.)	1.26
■ Width (mm)	32.0
■ CE Compliant	Yes
■ Duct Size W x H (In.)	1.26 x 2.12
■ Duct Size W x H (mm)	32.0 x 53.8
■ Mounting Method	Standard Mounting Holes
■ Pricing Description	Slotted Duct, PVC, 1"x2"x6", BLK
■ Slot Width (In.)	0.31
■ Slot Width (mm)	7.9
■ Cover Part Number	C1BL6
■ Min. Order UOM	FT
■ Min. Order Qty.	6
■ BOM Qty. (# of Pkgs.)	0
■ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.