

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130108-0146

Status:

Active

Description:

Super-Safeway™ 40W Fluorescent Machine Light, Screw Mount with 18/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')




Series

image - Reference only

EU RoHS

Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
130108Series

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA	LR85374
UL	E174254

General

Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	None
Product Literature Order No	987650-8054
Product Name	Super-Safeway™
Type	Wide Area Lamps
UPC	78678861263
Woodhead	Yes

Physical

Cord Length - Primary	4.57m (15.0')
Cord Length - Secondary	N/A
Depth	76.20mm (3.000")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	57.15mm (2.250")
Length	798.83mm (31.450")
Material - Globe	Clear Polycarbonate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Screw-Bracket
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTOOW
Lamp Type	PL-L 40/41
Lamp Wattage - Maximum	40W
Lumens	2970
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number	1097-3M
-----------------	---------

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION