

PRODUCT DATASHEET

Heavy Duty Flashlight **Energizer** INDUSTRIAL⁺

1251

DURABLE

- Survives a 1-meter drop
- Resists staining and corrosion



WEATHERPROOF

- Meets requirements for IEC60529 IPX4 rating
- Light continues to operate after being exposed to splashing water from any direction



NON-CONDUCTIVE

- Protects user from immediate electric shock



USEFUL

- Intense beam shines useable light on objects up to 70 meters away



Ideal for wet areas, the 1251 is weatherproof and shockproof. A built-in hanger ring makes it easy to keep this sturdy light within reach.

An impact-resistant housing reduces the chance of breakage from dropping and abuse and the chemical-resistant polypropylene body protects it from staining and corrosion. This light is a great choice for demanding job site conditions.




Before Using Your Flashlight:
Please read all instructions and cautionary markings on the package and light

Product Detail:

Designation:	Energizer Industrial Heavy Duty Flashlight
Model:	1251
Color:	Yellow
Power Source:	Two "D"
ANSI/NEDA:	Series 13
Lamp:	KPR-102
Lamp Rating:	2.4V, 0.5A
Lamp Life (hr):	15
Lamp Output (lumens):	16
Beam Distance (m):	70
Peak Beam Intensity (cd):	1,225
Run Time (h:mm):	12:15
Typical Weight:	113 grams without batteries
Dimensions (mm):	203 x 60.5

Performance:



Tested according to ANSI/NEMA FL 1 Standards.

Important Notice

This datasheet contains information specific to products manufactured at the time of its publication
Contents herein do not constitute a warranty
©Energizer / All Rights Reserved