





C	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT HEAD FINISHED IN BLACK EPOXY PAINT
D	RED GLASS FILLED POLYESTER HOUSING AND COVER, ZINC DIECAST HEAD FINISHED IN BLACK EPOXY PAINT
E	ZINC DIECAST BODY AND HEAD WITH STEEL COVER, BODY AND COVER FINISHED IN RED EPOXY PAINT, HEAD FINISHED IN BLACK EPOXY PAINT 3 - CONDUIT)



AVAILABLE IN GSC, GSD, AND GSE		AVAILABLE IN GSE ONLY	
01	SNAP-ACTION CONTACTS	40	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
07	SNAP-ACTION CONTACTS (GOLD PLATED CONTACTS)	41	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
03	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	42	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
33	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)	43	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
06	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED)	44	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)
36	SLOW-ACTION CONTACTS (2 NORMALLY CLOSED) (GOLD PLATED CONTACTS)	45	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)
46	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE)	47	SLOW-ACTION CONTACTS (BREAK BEFORE MAKE) (GOLD PLATED CONTACTS)



CONTACT CLOSED

CONTACT OPEN

** POSITIVE OPENING TO IEC 947-5-1

ELECTRICAL RATING - I _{th} = 10A					ENVIRONMENTAL		APPROVALS
SILVER CONTACTS				GOLD PLATED CONTACTS			
AC FOR SWITCH CODES 01, 07, 03, 33	AC FOR SWITCH CODES 06, 36	AC FOR SWITCH CODES 40,41,42,43,44,45,46,47	DC				
A600 AC15 U _e I _e	A500 AC15 U _e I _e	A300 AC15 U _e I _e	Q300 DC13 U _e I _e				
VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4 600 1.2	VOLTS AMPS 120 6 240 3 380 1.9 480 1.5 500 1.4	VOLTS AMPS 120 6 240 3	VOLTS AMPS 125 0.55 250 0.27	1V 10uA MIN 50V 100mA MAX	IP66 NEMA 1, 4, 12, 13 TEMP RANGE: -40°C TO +85°C -40°F TO +185°F STORAGE: -40°C TO +85°C -40°F TO +185°F SHOCK: 50G PER IEC 68-2-27 VIBRATION: 100G PER IEC 68-2-6		 IEC 947-5-1 EN50047 

