

Specifics **OBSOLETE- USE PFD-35N29WQ**

Oscillation Frequency (Hz)	2900 ± 500
Operating Voltage (VDC)	3 ~ 28
Rated Voltage (VDC)	12
Current Consumption Max. (mA)	8 at Rated Voltage
Sound Pressure Level Min. (dB)	90 at 30cm at Rated Voltage
Tone / Pulse Rate	Constant + Fast Pulse 3.0 ±20%
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +80
Housing	ABS 777D plastic resin (Color : Black)
Leading Wire	28 AWG
Weight (Grams)	14.2
Options	For other options contact factory

Dimensions: (units: mm)