

Cup Brushes Record

These multi-purpose brushes with a crimped wire fill are ideally suited for use on bench machines, one-hand angle grinders, large angle grinders and pneumatic grinders. We can supply them with a threaded or plain arbor hole to suit your machine.

Type 1.6602 is produced with a plastic cap.

Fill types: RECORD



STD – Steel wire, natural hard, crimped.

INOX – Stainless steel wire, acid resistant, crimped.

MES – Brass wire (Cu-Zn), crimped.

Applications:

Removal of rust, corrosion, paint and primer and generally to produce clean surfaces.



Cup Brushes Record



Wear eye protection!

RPM/
UPM

Type

Topfbürsten Record

Dimensions/
Abmessungen

Ø	L	d	d			0.30 MES	0.20 STD	0.30 STD	0.50 STD
mm	mm	min.	max.		max.	Art.-No.	Art.-No.	Art.-No.	Art.-No.
60 (2 3/8")	18	–	–	M 8	11000	T1.4602	9901.0562	9901.0493	9901.0547
	16	–	–	M 10	11000	T1.6602	9901.0563	9901.0495	9901.0522
	16	–	–	M 12 x 1,5	11000	T1.6602	9901.0230	9901.0494	9901.0027
	16	–	–	M 14	11000	T1.6602	9901.0094	9901.0032	9901.0005
75 (3")	20	–	–	M 14	9000	T1.8752	9901.0141	9901.0074	9901.0516
	20	–	–	UNC 5/8"	9000	T1.8752	9901.0565	9901.0497	9901.0498
80 (3")	25	10	16	d ₁ 20,0	8500	T282	9424.6513	9424.0313	9424.0513
	25	–	–	M 14	8500	T282	9404.6513	9404.0313	9404.0513
	25	–	–	UNC 5/8"	8500	T282	9406.6513	9406.0313	9406.0513
100 (4")	30	10	25	d ₁ 22,2	8500	T3102	9434.6517	9434.0317	9434.0517
	30	–	–	M 14	8500	T3102	9494.6517	9494.0317	9494.0517
	30	–	–	UNC 5/8"	8500	T3102	9496.6517	9496.0317	9496.0517
125 (5")	35	10	32	d ₁ 22,2	6500	T4122	9444.6522	9444.0322	9444.0522
	35	–	–	M 14	6500	T3122	9494.6522	9494.0322	9494.0522
	35	–	–	UNC 5/8"	6500	T3122	9496.6522	9496.0322	9496.0522
150 (6")	55	10	32	d ₁ 22,2	6500	T4152	9444.6527	9444.0327	9444.0527
	55	–	–	M 14	6500	T3152	9494.6527	9494.0327	9494.0527
	55	–	–	UNC 5/8"	6500	T3152	9496.6527	9496.0327	9496.0527