


Distributed by:



www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 175396

空心直流马达 Coreless DC motor	型号 Mode	OTL-4AL	
	外形尺寸 Dimension	(Ø4×14.0) 	
1、技术要求 Standard specification	单位 Unit	标准值 Standard	平均值 Average
1-1 电压/Voltage	DC, V	1.3	1.3
1-2 额定转速 Rated speed	r/min	8500±1500	8500
1-3 额定电流 Rated current	mA	80 Max	65
1-4 堵转电流 Stall current	mA	100 Max	95
1-5 起动电压 (瞬间作用力) Starting Voltage (instant apply)	DC, V	0.9 Max	0.8
1-6 端子阻抗 Terminal resistance	Ω	13±10%	13.0
1-7 转动方向 Direction of rotation		CW	CW
2、机械结构 Mechanical structure			
2-1 重量 Weight (approximately)	g	1.4	1.4
2-2 轴向间隙 End play of shaft	mm	0.1~0.2	0.15
2-3 偏心轮半径 Eccentric wheel radius	mm	R1.9	R1.9