



- 1) Tapered thread end max. 4P
- 2) Trilobular cross-section

BN 13916

Hexalobular (6 Lobe) socket pan head thread forming screws

~type C, metric thread

Steel case-hardened 450-560 HV

zinc plated blue, added lubricant



ISO 4042

Quenched and tempered fasteners ≥ 360 HV and tempered case-hardened fasteners with electroplated coatings: Susceptible to hydrogen embrittlement!

Further notice to residual risks can be found in the introduction section.



[3D Cadenas](#)



Application: steel, aluminum, aluminum die-casting, zinc, zinc die-casting, non ferrous materials.

A technical brochure is available on request.

Article#	d ₁	d ₂ max.	k max.		t max.	A~	L
3271292	M2	4	1,72	X6	0,8	1,8	3
3271294							4
3271295							5
3271296							6
3271297							8
3271298							10
3271299							12
3058892	M2,5	5	2,12	X8	1,2	2,4	4
3059288							5
3059290							6
3059292							8
3059295							10
3059296							12
3271300							16
3271301							20
3646185	M3	6	2,52	X10	1,3	2,8	4
2027526							5
2027534							6
2027542							8
2027550							10
2027569							12
3646186							14
3059300							16
3271302							20
3271303							25

3271304								30
---------	--	--	--	--	--	--	--	----

Article#	d ₁	d ₂ max.	k max.		t max.	A~	L
3377397	M4	8	3,25	X20	1,8	3,9	5
2027577							6
2027585							8
2027593							10
2027607							12
3646187							14
2027615							16
3070342							20
3070341							25
3271305							30
3271306							35
3271307							40
2027623	M5	10	3,95	X25	2	4,5	8
2027631							10
2027658							12
3646188							14
2027666							16
2027674							20
3070340							25
3271308							30
3271309							35
3271310							40
3646189	M6	12	4,75	X30	2,4	5,6	8
2027682							10
2027844							12
2027704							16
2027712							20
2027720							25
3271311							30
3271312							35
3271313							40
3271314	M8	16	6,15	X40	3,3	6,8	16
3271315							20
3271317							25
3271319							30
3271320							35
3271321							40