

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1202340016

Status:

Active

Overview:

Brad M23 Signal and Power Connectors

Description:

Brad M23 Power Connector, Front Panel-Mount Receptacle, 90° Male, Flange Mount
4xØ 3.20mm, Rotatable Flange 28x28mm, without Contacts, 8 (4+3+PE) Poles

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120234
Application	Power
Comments	without Contacts, without Contacts
IP Rating	IP67
Material - Contact	Brass
Overview	Brad M23 Signal and Power Connectors
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906301729
Physical	
Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight
Poles	8 (4+3+PE)
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	28.0A
Voltage - Maximum	600V
Material Info	
Engineering Number	KRP8G07-0052
Reference - Drawing Numbers	
Sales Drawing	SD-120234-004



Series image - Reference only

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

120234 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION