


Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriete de c FCI. Droits de reproduction FCI.

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.


PRODUCT NUMBER
SEE TABLE

FIGURE 1




4X R/A RECEPTACLE ASSEMBLY
WITHOUT MOUNTING TABS

FIGURE 2




12X R/A RECEPTACLE ASSEMBLY
WITHOUT MOUNTING TABS

FIGURE 3



4X R/A RECEPTACLE ASSEMBLY
WITH MOUNTING TABS


FIGURE 4



12X R/A RECEPTACLE ASSEMBLY
WITH MOUNTING TABS


LATCH STYLE

FIGURE 5




4X R/A RECEPTACLE ASSEMBLY

FIGURE 6



12X R/A RECEPTACLE ASSEMBLY

THUMBSCREW STYLE





DETAIL A
SCALE 10:1

(TYPICAL LOCATION ON ALL STYLES OF EYEMAX
R/A RECEPTACLE ASSEMBLIES FOR PLACEMENT
OF INFORMATION, SEE NOTE 1)

NOTES:

1. TYCO LOGO AND LOT CODE TO BE PLACED APPROXIAMETLY AS SHOWN.
2. HOUSING MATERIAL: UL94 V-0 LCP RESIN.
SIGNAL MATERIAL: COPPER ALLOY.
GROUND CONTACT MATERIAL: COPPER ALLOY.
3. PRODUCT SPECIFICATION: GS-12-209.
4. APPLICATION SPECIFICATION: GS-20-025.

rev	ecn no	dr	date
A	V03-0965	GIP	09/10/03
B	V05-0527	TAB	06/03/05
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

 www.fciconnect.com			surface 3.2 ASME Y14.5	tolerance ASME Y14.5	projection 	MM 
Dr	G.PETERS	09/05/03	Product family	EyeMax (tm)	size	Scale
Eng	D.BRANN	09/10/03	Spec ref	-	A3	2:1
Chr	D.BRANN	09/10/03	Material	SEE NOTES	ECN	V05-0527
Appr	D.BRANN	09/10/03				
title EYEMAX(tm) RECEPTACLE for TYCO PRIVATE LABEL			dwg no 10033804			Rev. B
catalog no			CUSTOMER			sheet 1 of 3

Tous droits strictement reserves. Reproduction ou communication o des liers interdite sous quelque forme que ce soit sans autorisation ecrite du proprietaire. Propriete de c FCI. Droits de reproduction FCI.

FCI

C

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FIGURE 1 4X RECEPTACLE ASSEMBLY w/o MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-001	1.6mm	NO	TAPE & REEL
10033804-002	1.6mm	NO	TRAY
10033804-003	1.6mm	YES	TAPE & REEL
10033804-004	1.6mm	YES	TRAY
10033804-005	2.4mm	NO	TAPE & REEL
10033804-006	2.4mm	NO	TRAY
10033804-007	2.4mm	YES	TAPE & REEL
10033804-008	2.4mm	YES	TRAY
10033804-009	4.0mm	NO	TAPE & REEL
10033804-010	4.0mm	NO	TRAY
10033804-011	4.0mm	YES	TAPE & REEL
10033804-012	4.0mm	YES	TRAY

FIGURE 2 12X RECPTACLE ASSEMBLY w/o MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-301	1.6mm	NO	TAPE & REEL
10033804-302	1.6mm	NO	TRAY
10033804-303	1.6mm	YES	TAPE & REEL
10033804-304	1.6mm	YES	TRAY
10033804-305	2.4mm	NO	TAPE & REEL
10033804-306	2.4mm	NO	TRAY
10033804-307	2.4mm	YES	TAPE & REEL
10033804-308	2.4mm	YES	TRAY
10033804-309	4.0mm	NO	TAPE & REEL
10033804-310	4.0mm	NO	TRAY
10033804-311	4.0mm	YES	TAPE & REEL
10033804-312	4.0mm	YES	TRAY

FIGURE 3 4X RECEPTACLE ASSEMBLY w/ MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-101	1.6mm	NO	TAPE & REEL
10033804-102	1.6mm	NO	TRAY
10033804-103	1.6mm	YES	TAPE & REEL
10033804-104	1.6mm	YES	TRAY
10033804-105	2.4mm	NO	TAPE & REEL
10033804-106	2.4mm	NO	TRAY
10033804-107	2.4mm	YES	TAPE & REEL
10033804-108	2.4mm	YES	TRAY
10033804-109	4.0mm	NO	TAPE & REEL
10033804-110	4.0mm	NO	TRAY
10033804-111	4.0mm	YES	TAPE & REEL
10033804-112	4.0mm	YES	TRAY

LATCH STYLE CONNECTORS, FIGURES 1 THRU 4

FIGURE 4 12X RECEPTACLE ASSEMBLY w/ MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-401	1.6mm	NO	TAPE & REEL
10033804-402	1.6mm	NO	TRAY
10033804-403	1.6mm	YES	TAPE & REEL
10033804-404	1.6mm	YES	TRAY
10033804-405	2.4mm	NO	TAPE & REEL
10033804-406	2.4mm	NO	TRAY
10033804-407	2.4mm	YES	TAPE & REEL
10033804-408	2.4mm	YES	TRAY
10033804-409	4.0mm	NO	TAPE & REEL
10033804-410	4.0mm	NO	TRAY
10033804-411	4.0mm	YES	TAPE & REEL
10033804-412	4.0mm	YES	TRAY

FIGURE 5 4X RECEPTACLE ASSEMBLY			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-201	1.6mm	NO	TAPE & REEL
10033804-202	1.6mm	NO	TRAY
10033804-203	1.6mm	YES	TAPE & REEL
10033804-204	1.6mm	YES	TRAY
10033804-205	2.4mm	NO	TAPE & REEL
10033804-206	2.4mm	NO	TRAY
10033804-207	2.4mm	YES	TAPE & REEL
10033804-208	2.4mm	YES	TRAY
10033804-209	4.0mm	NO	TAPE & REEL
10033804-210	4.0mm	NO	TRAY
10033804-211	4.0mm	YES	TAPE & REEL
10033804-212	4.0mm	YES	TRAY

FIGURE 6 12 RECEPTACLE ASSEMBLY			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
10033804-501	1.6mm	NO	TAPE& REEL
10033804-502	1.6mm	NO	TRAY
10033804-503	1.6mm	YES	TAPE & REEL
10033804-504	1.6mm	YES	TRAY
10033804-505	2.4mm	NO	TAPE & REEL
10033804-506	2.4mm	NO	TRAY
10033804-507	2.4mm	YES	TAPE & REEL
10033804-508	2.4mm	YES	TRAY
10033804-509	4.0mm	NO	TAPE & REEL
10033804-510	4.0mm	NO	TRAY
10033804-511	4.0mm	YES	TAPE & REEL
10033804-512	4.0mm	YES	TRAY

THUMBSCREW STYLE CONNECTORS, FIGURES 5 & 6.

EYEMAX(tm) RECEPTACLE for TYCO PRIVATE LABEL		dwg no 10033804	Rev. B
catalog no -		CUSTOMER	sheet 2 of 3

Tous droits strictement reserves. Reproduction ou communication a des tiers interdite sous quelque forme que ce soit sans autorisation écrite du propriétaire. Propriété de c FCI. Droits de reproduction FCI.

FCI

All rights strictly reserved. Reproduction or issue to third parties in any form whatever is not permitted without written authority from the proprietor. Property of FCI. Copyright FCI.

FIGURE 1 4X RECEPTACLE ASS'Y w/o MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-001LF	1.6mm	NO	TAPE & REEL
I0033804-002LF	1.6mm	NO	TRAY
I0033804-003LF	1.6mm	YES	TAPE & REEL
I0033804-004LF	1.6mm	YES	TRAY
I0033804-005LF	2.4mm	NO	TAPE & REEL
I0033804-006LF	2.4mm	NO	TRAY
I0033804-007LF	2.4mm	YES	TAPE & REEL
I0033804-008LF	2.4mm	YES	TRAY
I0033804-009LF	4.0mm	NO	TAPE & REEL
I0033804-010LF	4.0mm	NO	TRAY
I0033804-011LF	4.0mm	YES	TAPE & REEL
I0033804-012LF	4.0mm	YES	TRAY

FIGURE 2 12X RECEPTACLE ASS'Y w/o MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-301LF	1.6mm	NO	TAPE & REEL
I0033804-302LF	1.6mm	NO	TRAY
I0033804-303LF	1.6mm	YES	TAPE & REEL
I0033804-304LF	1.6mm	YES	TRAY
I0033804-305LF	2.4mm	NO	TAPE & REEL
I0033804-306LF	2.4mm	NO	TRAY
I0033804-307LF	2.4mm	YES	TAPE & REEL
I0033804-308LF	2.4mm	YES	TRAY
I0033804-309LF	4.0mm	NO	TAPE & REEL
I0033804-310LF	4.0mm	NO	TRAY
I0033804-311LF	4.0mm	YES	TAPE & REEL
I0033804-312LF	4.0mm	YES	TRAY

FIGURE 3 4X RECEPTACLE ASS'Y w/ MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-101LF	1.6mm	NO	TAPE & REEL
I0033804-102LF	1.6mm	NO	TRAY
I0033804-103LF	1.6mm	YES	TAPE & REEL
I0033804-104LF	1.6mm	YES	TRAY
I0033804-105LF	2.4mm	NO	TAPE & REEL
I0033804-106LF	2.4mm	NO	TRAY
I0033804-107LF	2.4mm	YES	TAPE & REEL
I0033804-108LF	2.4mm	YES	TRAY
I0033804-109LF	4.0mm	NO	TAPE & REEL
I0033804-110LF	4.0mm	NO	TRAY
I0033804-111LF	4.0mm	YES	TAPE & REEL
I0033804-112LF	4.0mm	YES	TRAY

LATCH STYLE CONNECTORS, FIGURES 1 THRU 4

FIGURE 4 12X RECEPTACLE ASS'Y w/ MNTG. EARS			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-401LF	1.6mm	NO	TAPE & REEL
I0033804-402LF	1.6mm	NO	TRAY
I0033804-403LF	1.6mm	YES	TAPE & REEL
I0033804-404LF	1.6mm	YES	TRAY
I0033804-405LF	2.4mm	NO	TAPE & REEL
I0033804-406LF	2.4mm	NO	TRAY
I0033804-407LF	2.4mm	YES	TAPE & REEL
I0033804-408LF	2.4mm	YES	TRAY
I0033804-409LF	4.0mm	NO	TAPE & REEL
I0033804-410LF	4.0mm	NO	TRAY
I0033804-411LF	4.0mm	YES	TAPE & REEL
I0033804-412LF	4.0mm	YES	TRAY

FIGURE 5 4X RECEPTACLE ASS'Y			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-201LF	1.6mm	NO	TAPE & REEL
I0033804-202LF	1.6mm	NO	TRAY
I0033804-203LF	1.6mm	YES	TAPE & REEL
I0033804-204LF	1.6mm	YES	TRAY
I0033804-205LF	2.4mm	NO	TAPE & REEL
I0033804-206LF	2.4mm	NO	TRAY
I0033804-207LF	2.4mm	YES	TAPE & REEL
I0033804-208LF	2.4mm	YES	TRAY
I0033804-209LF	4.0mm	NO	TAPE & REEL
I0033804-210LF	4.0mm	NO	TRAY
I0033804-211LF	4.0mm	YES	TAPE & REEL
I0033804-212LF	4.0mm	YES	TRAY

FIGURE 6 12X RECEPTACLE ASS'Y			
TYCO LOGO PART NUMBER	P.C.B. THICKNESS	LOCATING PEGS	PACKAGING
I0033804-501LF	1.6mm	NO	TAPE& REEL
I0033804-502LF	1.6mm	NO	TRAY
I0033804-503LF	1.6mm	YES	TAPE & REEL
I0033804-504LF	1.6mm	YES	TRAY
I0033804-505LF	2.4mm	NO	TAPE & REEL
I0033804-506LF	2.4mm	NO	TRAY
I0033804-507LF	2.4mm	YES	TAPE & REEL
I0033804-508LF	2.4mm	YES	TRAY
I0033804-509LF	4.0mm	NO	TAPE & REEL
I0033804-510LF	4.0mm	NO	TRAY
I0033804-511LF	4.0mm	YES	TAPE & REEL
I0033804-512LF	4.0mm	YES	TRAY

THUMBSCREW STYLE CONNECTORS, FIGURES 5 & 6.

- NOTES:
1. LEAD FREE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
 2. THE HOUSING WILL WITHSTAND EXPOSURE TO 260° C PEAK TEMPERATURE FOR 15 SECONDS IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
 3. PACKAGING OF LEAD FREE PRODUCTS MEETS LABELING AND PACKAGING SPECIFICATIONS GS-14-920.
 4. PLATING: LEAD FREE SOLDER TAILS 2μm (80μin) MIN MATTE TIN OVER 1.27μm (50μm) MIN NICKEL UNDERPLATE.

EYEMAX(tm) RECEPTACLE for TYCO PRIVATE LABEL	dwg no 10033804	Rev. B
catalog no	CUSTOMER	sheet 3 of 3