


STRADA-DW-OSL LENSES FOR OSRAM OSOLON SSL/SX LEDs

OSRAM
www.osram.com



- Specially designed for Osram Osolon series of LEDs.
- New extremely wide SIDE-EMITTING design with very and uniform light distribution.
- Comes with integrated positioning pins.
- Lens material optical grade PMMA with high UV and temperature resistance (105°C/220°F). Allows use of high current and temperature conditions
- Best available optical efficiency, approximately 92%.
- Fastening to heat sink with or without PU foam adhesive tape of automotive grade, please select which suits the best for your needs.
- Please check fastening details from this link:
(http://www.ledil.com/datasheets/DataSheet_TAPE.pdf)

LENS TYPES


NAME	ORDERING CODE	FWHM Angle
Strada-DW-OSL	C11255_Strada-DW-OSL	±46° x ±71°
Strada-DW-OSL-TAPE	CA11256_Strada-DW-OSL-tape	±46° x ±71°

NAME	ORDERING CODE	FWHM Angle
Strada-DW-OSL	C11255_Strada-DW-OSL-SX	To be measured shortly
Strada-DW-OSL-TAPE	CA11256_Strada-DW-OSL-SX-tape	To be measured shortly


© Ledil Oy – PRELIMINARY - Subject to change without prior notice

MEASUREMENT DATA & DRAWING

Relative Intensity of C11255_Strada-DW-OSL



© Ledil Oy – PRELIMINARY - Subject to change without prior notice



© Ledil Oy – PRELIMINARY - Subject to change without prior notice