



General ordering data

Order No.	1720500000
Part designation	VG 13,5-K68 SKS
Version	Cable gland, Polyamide 6, RAL 7035, External thread: PG 13.5
EAN	4008190358716
Qty.	50 pc(s).

General details

AF size 1	24 mm
Assembly temperature, max.	80 °C
Assembly temperature, min.	-30 °C
Clamping range, max.	12 mm
Clamping range, min.	6 mm
External thread	PG 13.5
Length	105 mm
Length of thread	9 mm
Material	Polyamide 6
Protection class	IP 68 - 5 bar
RAL colour	RAL 7035
Type of cable gland	PG

Approvals

Approvals institutes



Classifications

ETIM 2.0	EC000441
ETIM 3.0	EC000441
eClass 4.1	27-14-12-09
eClass 5.0	27-14-91-09
eClass 5.1	27-14-91-09

Classifications

Similar products

Order No.	Part designation	Version
1776700000	VGM12-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: M 12 x 1.5
1776710000	VGM16-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: M 16 x 1.5
1776720000	VGM20-K68 SKS 10,0-14,0	Cable gland, Polyamide 6, RAL 7035, External thread: M 20 x 1.5
1778860000	VGM20-K68 SKS 6,0-12,0	Cable gland, Polyamide 6, RAL 7035, External thread: M 20 x 1.5
1776730000	VGM25-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: M 25 x 1.5
1720490000	VG 11-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: PG 11
1720510000	VG 16-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: PG 16
1720520000	VG 21-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: PG 21
1720480000	VG 9-K68 SKS	Cable gland, Polyamide 6, RAL 7035, External thread: PG 9