




断面 A-A
SECT.




注記

- 製品規格 : 108-5174
- 取付通用規格 : 114-5076
- 相当品 P/N : 181270-1



断面 C-C
SECT.



断面 D-D
SECT.

NOTES

- PRODUCT SPEC. : 108-5174
- APPLICATION SPEC. : 114-5076
- SIMILAR TO 181270-1

752936-1	172788-1	0.38 Au PL. ON CONTACT AREA - OTHERS ARE NI PL. 接触部 0.38μ以上の部分金めっき 残部ニッケルめっき	172790-1
HAND TOOL No 手動工具 No	STRIP P/N 連鎖状端子	仕上 FINISH	型番 P/N
		0.1982 BY AMP Japan Ltd. ALL RIGHTS RESERVED AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING	参考図面 (CUSTOMER COPY REFERENCE ONLY)
MATERIAL PHOS-BR. リン青銅 0.22t		TRADE MARK	
SEE TABLE 表参照		日本イー・エム・ピー株式会社 TOKYO, JAPAN	
0.12 ~ 0.38 (AWG 22-#26)		WIRE CLASS	
0.9 ~ 1.55 (mm)		WIRE TYPE	
TOLERANCE EXCEPT AS NOTED		LOC SIZE 番号 NO	
J A		C-172790	
REC. CONTACT, AMP MOD. MOD. II CRIMP-ON SNAP-IN P/N モジュ モデル II 圧着型 コンタクト			

0, REVISED (ECN No J84-7505) J.C. S.M. 2-13-84
0 RELEASED (ECN No J82-6500) S.M.

LTR 変更 (REVISION RECORD) DR CHK DATE

DR 5-17-82 DE 5-17-82
CHK 5-17-82 APP 5-17-82