GREENLEE®
A Textron Company

MADE FOR THE TRADE™

12" HEAVY-DUTY HACK SAW

FEATURING BIMETAL BLADE

LIFETIME LIMITED WARRANTY

12" HEAVY-DUTY HACK SAW

	FEATURES	BENEFITS
1	Additional Grip	To allow two hand sawing.
2	Recip Blade Holder	For additional versatility.
3	Two Angle Blade Holder	Allows straight cuts and 45° flush cuts.
4	Easy Blade Adjustment	Allows blade tension adjustments up to 30,000 PSI.
5	Overmolded Grip	For comfort and slip resistance.
6	Blade Storage	For easy blade storage and access.

Note: This is not an insulated tool.

12" Heavy-Duty Hack Saw

CAT. NO.	UPC NO.	DESCRIPTION
333A	56302	12" Heavy-Duty Hacksaw
333-1218	10037	12" (30.5 cm) Bimetal Blade, 18 Teeth per Inch
333-1224	10038	12" (30.5 cm) Bimetal Blade, 24 Teeth per Inch
333-1232	10039	12" (30.5 cm) Bimetal Blade, 32 Teeth per Inch

SPECIFICATIONS

Overall Length	15-3/4" (40.0 cm)
Weight	2.15 lbs. (.98 kg)
Blade Tension	30 KSI

USA Tel: 800.435.0786 Fax: 800.451.2632
Canada Tel: 800.435.0786 Fax: 800.524.2853
International Tel: +1.815.397.7070 Fax: +1.815.397.9247

GREENLEE®
A Textron Company

4455 BOEING DRIVE, ROCKFORD, IL 61109-2988 USA
GENERAL OFFICES: 815.397.7070

www.greenlee.com

MA-4907 11/06 ©2006 Greenlee Textron Inc.
Greenlee Textron Inc. is a subsidiary of Textron Inc.