

Quick-Set Test Indicators - Series 513

Features

- Anti-magnetic
- Jeweled bearings
- No-clutch structure
- Water and dust resistant
- Glare-free crystal with scratch-resistant coating
- Metric dial faces in yellow
- The most direct gear train design ever applied to Test Indicators means—higher level of sensitivity, reliability, repeatability and accuracy throughout tool life.



Inch	Inch/Metric	Metric												
Order Number	513-282	513-402	513-402T	513-403	513-403T	513-412	513-412T	513-452	513-452T	513-453	513-453T	513-462	513-463	513-982
Image	-	-	-	-	-		-	-	-		-	-	-	-
Parts Break Down	-	-	-	-	-	-	-	-	-	-	-	-	-	-
Accuracy	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0001in	0.0005in
Dial Reading	0-15-0	0-15-0	0-15-0	0-4-0	0-4-0	0-15-0	0-15-0	0-15-0	0-15-0	0-4-0	0-4-0	0-15-0	0-4-0	0-15-0
Graduation	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0001in	0.0005in
Measuring Force	0.03-in	0.03-in	0.03-in	0.008-in	0.008-in	0.03-in	0.03-in	0.03-in	0.03-in	0.008-in	0.008-in	0.03-in	0.008-in	0.03-in
Remarks	-	-	-	-	-	Long Point	Long Point	-	-	Mini-Dial	-	Mini-Dial	Mini-Dial	-
Type	Parallel	Horizontal	Horizontal	Horizontal	Horizontal	Horizontal	Horizontal	Vertical	Vertical	Vertical	Vertical	Horizontal	Horizontal	Parallel

Pages: [1](#)

Inch	Inch/Metric	Metric		
Order Number	513-406	513-406T		
Image		-		
Parts Break Down	-	-		
Graduation	0.0005in 0.01mm	0.0005in 0.01mm		
Range	0.03-0.7in 0-0.7mm	0.03-0.7in 0-0.7mm		
Dial Reading	0-15-0,0-35-0	0-15-0,0-35-0		
Accuracy	0.0005in	0.0005in		
Type	Horizontal	Horizontal		
Remarks	Combitec Anti-Magnetic	Combitec Anti-Magnetic		

Pages: [1](#)

Inch	Inch/Metric	Metric								
Order Number	513-404E	513-404T	513-405E	513-405T	513-414E	513-414T	513-415E	513-415T	513-454T	513-455T
Image	-	-		-	-	-	-	-	-	-
Parts Break Down	-	-		-	-	-	-	-	-	-
Graduation	0.01	0.01	0.002	0.002	0.01	0.01	0.01	0.01	0.01	0.002
Dial Reading	0-40-0	0-40-0	0-100-0	0-100-0	0-25-0	0-25-0	0-50-0	0-50-0	0-40-0	0-100-0
Measuring Force	0.08-mm	0.08-mm	0.02-mm	0.02-mm	0.05-mm	0.05-mm	1-mm	1-mm	0.08-mm	0.02-mm
Accuracy	0.008mm	0.008mm	0.003mm	0.003mm	0.01mm	0.01mm	0.01mm	0.01mm	0.008mm	0.003mm
Type	-	-	-	-	-	-	-	-	-	-

Pages: [1](#)