

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

75477-5001

Status:

Active

Overview:

SFP+ and SFP Interconnect Solutions

Description:

Small Form-factor Pluggable (SFP) Stacked 2-by-6 Multi-Port Connector with Press-fit PC Tails, 240 Circuits, Lead-Free




image - Reference onlySeries

Documents:

3D Model

Drawing (PDF)

Product Specification PS-75310-001 (PDF)

Application Specification AS-75310-001 (PDF)

Application Specification AS-76090-001 (PDF)

Packaging Specification PK-75451-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

I/O Connectors

Series

75477

Application

Module-to-Board

Component Type

Receptacle

Overview

SFP+ and SFP Interconnect Solutions

Product Name

SFP

Type

N/A

UPC

822350235549

Physical

Boot Color

N/A

Circuits (Loaded)

240

Circuits (maximum)

240

Color - Resin

Black

Durability (mating cycles max)

100

Flammability

94V-0

Gender

Female

Lock to Mating Part

Yes

Material - Metal

High Performance Alloy (HPA)

Material - Plating Mating

Gold

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

124.856/g

Number of Rows

2

Orientation

Right Angle

PC Tail Length

2.07mm

PCB Locator

Yes

PCB Retention

Yes

PCB Thickness - Recommended

1.60mm

Packaging Type

Tray

Panel Mount

No

Pitch - Mating Interface

0.80mm

Pitch - Termination Interface

0.80mm

Plating min - Mating

0.762µm

Plating min - Termination

0.762µm

Polarized to Mating Part

Yes

Polarized to PCB

Yes

Ports

12

Surface Mount Compatible (SMC)

No

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

75477Series

Use With

75951-0999 SFP Dust Plug

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
2-by-6 SFP Stacked Multi-Port Insertion Tool	0622030155
Stacked Multi-Port Extraction Tool, 2 by 6	0622029950

Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No
Electrical	
Current - Maximum per Contact	0.5A
Shield Type	EMI Fingers
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-75310-001, AS-76090-001
Packaging Specification	PK-75451-001
Product Specification	PS-75310-001
Sales Drawing	SD-75477-001, SD-75477-101

This document was generated on 09/02/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

75477-5001