




1. RECEPTABLE ACCEPTS AN 0.20-0.36 [.008-.014] THK I.C. LEAD.
- 2 MATERIAL: HOUSING-GLASS FILLED THERMOPLASTIC, 94V-0, BLACK
3. TUBE LOADED.
- 4 TWO 0.00076 [.000030] MIN THK GOLD STRIPES IN CONTACT AREA, TIN-LEAD (93-7) ON CONTACT LEGS, BALANCE OF CONTACT NICKEL PLATED.

SECTION A-A
ROTATED 90° CW
SCALE 10:1

TINNED	PHOS.BRZ. 0.15[.006] THK		2-382718-3
4	BE.CU. 0.15[.006] THK		2-382718-2
TINNED	BE.CU. 0.15[.006] THK		2-382718-1
CONTACT PLATING	CONTACT MATERIAL	HOUSING MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN C. WHITT 23 OCT 92		AMP AMP Incorporated Harrisburg, PA 17105-3608	
				CHK R. TALLEY 03 NOV 92			
DIMENSIONS: mm (INCHES)		TOLERANCES UNLESS OTHERWISE SPECIFIED.		APVD F. ROYD 06 NOV 92		NAME	
		0 PLC ±=		PRODUCT SPEC		SOCKET ASSY, DIP, LADDER, 28 POS, DIPLOMATE DL	
		1 PLC ±=		108-1066			
		2 PCL ±= (1.005)		APPLICATION SPEC			
		4 PCL ±=		114-1049			
MATERIAL SEE TABLE		FINISH SEE TABLE		WEIGHT -		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
				A1 00779 C-382718		-	
				CUSTOMER DRAWING			
				SCALE 5:1		SHEET 1 OF 1	
				REV 0			