


| PANEL THICKNESS |          | B    | L   | SCREW PROJECTION |     | T   | PART NUMBER  |
|-----------------|----------|------|-----|------------------|-----|-----|--------------|
| "A" MIN.        | "A" MAX. |      |     | P-1              | P-2 |     |              |
| .058            | .125     | .023 | .07 | .06              | .24 | .75 | 47-WO-2X2-Y2 |
|                 |          |      |     | .12              | .31 | .81 | 47-W1-2X2-Y2 |
|                 |          |      |     | .16              | .35 | .87 | 47-W2-2X2-Y2 |
|                 |          |      |     | .24              | .43 | .94 | 47-W3-2X2-Y2 |
| .125            | .188     | .062 | .14 | .12              | .31 | .81 | 47-WO-2X4-Y2 |
|                 |          |      |     | .16              | .35 | .87 | 47-W1-2X4-Y2 |
|                 |          |      |     | .24              | .43 | .94 | 47-W2-2X4-Y2 |
|                 |          |      |     | .16              | .35 | .87 | 47-WO-2X6-Y2 |
| .188            | .250     | .125 | .20 | .24              | .43 | .94 | 47-WO-2X6-Y2 |
|                 |          |      |     | .24              | .43 | .94 | 47-WO-2X6-Y2 |
| .250            | .312     | .188 | .26 | .24              | .43 | .94 | 47-WO-2X8-Y2 |
|                 |          |      |     | .24              | .43 | .94 | 47-WO-2X8-Y2 |


KNOB: 6262 ALUMINUM, NATURAL OR BLACK ORGANIC COATING.

SCREW: 1008 CASE HARDENED STEEL, ZINC PLATE  
CHROMATE PLUS SEALER OR BLACK ORGANIC COATING.  
FERRULE: 6061 ALUMINUM, NATURAL.  
SPRING: 302 STAINLESS STEEL, PASSIVATED.  
RATCHET MECHANISM: HARDENED STEEL, BLACK OXIDE.

1. PREPARE HOLE WITH COUNTERSINK ACCORDING TO THE REQUIRED "B" DIMENSION. RECOMMENDED MIN. DISTANCE FROM EDGE OF PANEL TO THE CENTERLINE OF THE HOLE IS .47.



**T-15 TORX®**



## **FASTENED**