

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [1301050049](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Watertite Wet Location 35W 12V Flood Light with Screw Release Guard, 14/2 SOOW, Overall Length 15.24m (50.0')

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

|                             |                                    |
|-----------------------------|------------------------------------|
| <b>Agency Certification</b> |                                    |
| CSA                         | LR85374                            |
| <b>General</b>              |                                    |
| Product Family              | Portable Lighting                  |
| Series                      | <a href="#">130105</a>             |
| NEMA Configuration          | Non-NEMA                           |
| Outlet                      | None                               |
| Overview                    | <a href="#">Specialty Lighting</a> |
| Product Name                | Watertite                          |
| Type                        | Hand Lamps, Specialty Light        |
| UPC                         | 78678835587                        |
| <b>Physical</b>             |                                    |
| Cord Length - Primary       | 15.24m (50.0')                     |
| Cord Length - Secondary     | N/A                                |
| Depth                       | N/A                                |
| Duty                        | Wet Location                       |
| Guard Included              | Yes                                |
| Guard Type                  | Screw Release                      |
| Height                      | 127.00mm (5.000")                  |
| Length                      | 228.60mm (9.000")                  |
| Material - Guard            | #10 Gauge Vinyl Coated Steel       |
| Mounting Style              | Hand Held                          |
| Packaging Type              | Carton                             |
| Socket Construction         | N/A                                |
| <b>Electrical</b>           |                                    |
| Bulb Type                   | Quartz Halogen                     |
| Cord Type - Secondary       | 14/2 SOOW                          |
| Lamp Type                   | PAR36                              |
| Lamp Wattage - Maximum      | 35W                                |
| Lumens                      | 350                                |
| On/Off Switch               | No                                 |
| Voltage (Fixture) - Maximum | 12V AC/DC                          |
| <b>Material Info</b>        |                                    |
| Engineering Number          | 1639-12                            |



Series image - Reference only

|                                                               |                   |
|---------------------------------------------------------------|-------------------|
| <b>EU ELV</b><br><b>Not Reviewed</b>                          |                   |
| <b>EU RoHS</b><br><b>Not Reviewed</b>                         | <b>China RoHS</b> |
| <b>REACH SVHC</b><br>Not Reviewed                             |                   |
| <b>Halogen-Free</b><br><b>Status</b><br><b>Not Reviewed</b>   |                   |
| For more information, please visit <a href="#">Contact US</a> |                   |
| China ROHS                                                    | Not Reviewed      |
| ELV                                                           | Not Reviewed      |
| RoHS Phthalates                                               | Not Reviewed      |

**Search Parts in this Series**  
[130105](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION