



**Dimensions: In.** (except where noted)

#### ■ Specifications:

- Exciting current: Input primary 120V 60Hz 45mA max.
- Primary rated voltage & frequency: 120V 60Hz
- HIPOT test: Input 60Hz 1500V for one minute between primary and secondary
- Insulation test: 500VDC 100MΩ min. between windings
- Temperature rise test: Less than 65°C for rated test with resistance method
- Maximum voltage: 6.0W

Rated Voltage	Rated Current	Load	No Load Voltage
3	28	210mA	4.3
4.5	43	400mA	7
6	48.6	430mA	9
7.5	55.5	430mA	11.3
9	61.6	430mA	13.5
12	77.6	430mA	18

Mooser Stock No.	Output Rating (mA)	Output Plug
412-3120	Universal 3, 4.5, 6, 7.5, 9 and 12VDC/500mA	6 way 2.5mm, 3.5mm male, 1.3mm3.5mm, 2.1mm5.0mm, 2.5mm5.5mm female 9VDC batt., snap, ± polarity switch

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[412-3120](#)