

PERFECT cable gland

50.6xx M/ASI/z


Configuration

Dome nut	Brass CuZn39Pb3, nickel-plated
Lamellar insert	Polyamide PA6 V-2
Sealing insert	Evoprene TPE
Gland body	Brass CuZn39Pb3, nickel-plated
O-ring	Nitrile rubber
Connecting thread	metric, as per EN 60423



Properties

Temperature range	-20°C +100°C
Protection grade	IP65
Comment	sealing inserts - see WJ-DM xx/ASI/z



Features

1xAS-i Bus-cable cable cross section left

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
M20x1,5	1 x AS-i Bus-Leitung	6	22	22	33,5	100	50.620 M/ASI/1
M25x1,5	1 x AS-i Bus-Leitung	7	27	27	36,5	50	50.625 M/ASI/1

2x AS-i Bus cable cable cross section twofold

A	ØC	L	SW1	SW2	H		Part No.
	mm	mm	mm	mm	mm	Piece	
M20x1,5	1 x AS-i Bus-Leitung	6	22	22	33,5	100	50.620 M/ASI/2
M25x1,5	1 x AS-i Bus-	7	27	27	36,5	50	50.625 M/ASI/2

A	ØC	L	SW1	SW2	H		Part No.
	mm Leitung	mm	mm	mm	mm	Piece	