



TL6100 SERIES TACT SWITCH



APPLICATIONS / MARKETS



Audio / Visual



Computer Peripherals



Consumer Electronics



Instrumentation



Telecommunication



Medical Equipment

RoHS

SPECIFICATIONS

Electrical Rating: 50mA @ 12VDC
Life Expectancy: per chart
Contact Resistance: 100mΩ Max. Initial
Insulation Resistance: 100 MΩ Min. at 100VAC
Dielectric Strength: 250VAC for 1 min.
Operating Temperature: -40°C to 85°C
Storage Temperature: -40°C to 85°C
Operating Force: 130 gf, 160 gf, 300 gf, 500 gf
Travel: 0.50mm
Contact Arrangement: SPST

FEATURES & BENEFITS

- Tube packaging
- Multiple operating forces
- Gold or silver contact option
- Multiple actuator lengths
- Process sealed

PART NUMBER CONFIGURATOR

Series	Actuator Options	Operating Force	Contact Plating	Termination
TL6100	A - 4.70mm B - 5.20mm C - 6.90mm D - 10.0mm	F130 - 130 gf F160 - 160 gf F300 - 300 gf F500 - 500 gf	Q - Silver R - Gold	P - PCB Pins

Actuation Force	Life Cycles
130 gf	1,000,000
160 gf	1,000,000
300 gf	500,000
500 gf	200,000

Specifications subject to change without notice



E-SWITCH®


www.e-switch.com

800.867.2717





2

TL6100 SERIES TACT SWITCH

BODY DIMENSIONS



Actuator	"L" Dimension
A	4.70
B	5.20
C	6.90
D	10.00



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[TL6105DF300QP](#) [TL6110BF160QP](#) [TL6110CF500QPSSDOME](#) [TL6120AF130QGSSDOME](#)
[TL6120AF160QGSSDOME](#) [TL6120AF300QGSSDOME](#) [TL6120BF160QGSSDOME](#) [TL6120CF160QG](#)
[TL6120CF300QG](#) [TL6110DF300QP](#) [TL6110BF130QP](#) [TL6110AF130QP](#) [TL6120BF130QG](#) [TL6120BF300QG](#)
[TL6110AF160QP](#) [TL6110CF160QP](#) [TL6120DF300QG](#) [TL6120AF160QG](#) [TL6110BF300QP](#) [TL6110DF160QP](#)
[TL6100AF130QP](#) [TL6100AF130QPSSDOME](#) [TL6100AF160QP](#) [TL6100AF300QP](#) [TL6100AF300QPSSDOME](#)
[TL6100BF130QP](#) [TL6100BF160QP](#) [TL6100BF300QP](#) [TL6100BF300RP](#) [TL6100CF130QP](#) [TL6100CF160QP](#)
[TL6100CF160QPSSDOME](#) [TL6100CF300QP](#) [TL6100DF130QP](#) [TL6100DF160QP](#) [TL6100DF160QPSSDOME](#)
[TL6100DF300QP](#) [TL6100DF300QPSSDOME](#) [TL6110AF300QP](#) [TL6110AF500QP](#) [TL6110BF500QP](#)
[TL6110CF300QP](#) [TL6110CF500QP](#) [TL6120AF130QG](#) [TL6120AF300RG](#) [TL6120AF500QG](#) [TL6120BF160RG](#)
[TL6120DF130QG](#) [TL6120DF160QG](#) [TL6120DF500QG](#) [TL6120DF500RG](#) [TL6105AF160QP](#) [TL6105BF160QP](#)
[TL6105DF160QP](#) [TL6190AF220RGRYCAPKIT](#) [TL6110DF160RP](#) [TL6110CF160RP](#)