

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [44262-6421](#)
Status: **Active**
Description: 5.33mm Pitch Crimp Terminal, Power Blade, Select Gold Strips over Tin

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Crimp Terminals
Series	44262
Application	Power
Crimp Quality Equipment	Yes
Product Name	N/A
UPC	800756811017
Physical	
Durability (mating cycles max)	500
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Gold
Net Weight	1.348/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.30mm
Wire Size AWG	14, 16
Wire Size mm²	N/A
Electrical	
Current - Maximum per Contact	20.0A
Voltage - Maximum	600V AC

Material Info

Reference - Drawing Numbers

Sales Drawing SD-44262-026




image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[44262Series](#)

Use With
[63832-6000](#) Crimp Applicator

Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i>	
Global	
Description	Product #
Hand Crimp Tool for 14-18 AWG Male and Female Power Contact Terminals	0638195500
Mini-Mac™ Applicator	0638326100