




- 1 HOUSING: LIQUID CRYSTAL POLYMER, COLOR BLACK.
CONTACTS: HIGH RELIABILITY COPPER ALLOY.
GROUND BUSES: BRASS,UNS C26000
- 2 CONTACTS & GROUND BUSES: NICKEL UNDERPLATE ALL OVER,
MATING SURFACE PLATED TO MEET LEVEL 2 PERFORMANCE
REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-1422,
SOLDER TAILS PLATED TIN-LEAD.
- 3 DATE CODE MARKED IN AREA INDICATED ON OPPOSITE SIDE OF
POSITION #1.
- 4 ONE GROUND BUS WITH 5 TAILS PER EACH MODULE.
- 5 TOLERANCE NON-ACCUMULATIVE.

3.000[76.2]	6	3.450[87.63]	3.898[99]	4.000[101.6]	266	767082-7
2.500[63.5]	5	2.950[74.93]	3.398[86.31]	3.500[88.9]	228	767082-6
2.000[50.8]	4	2.450[62.23]	2.898[73.61]	3.000[76.2]	190	767082-5
1.500[38.1]	3	1.950[49.53]	2.398[60.91]	2.500[63.5]	152	767082-4
1.000[25.4]	2	1.450[36.83]	1.898[48.21]	2.000[50.8]	114	767082-3
.500[12.7]	1	.950[24.13]	1.398[35.51]	1.500[38.1]	76	767082-2
.000[0]	0	.450[11.43]	.898[22.81]	1.000[25.4]	38	767082-1
E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL

1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005[0.13]

4 PLC ± -

ANGLES ± -

FINISH

2

DWN J. GERACE 4-7-98

CHK S. STRICKLER 4-7-98

APVD A. MONK 4-7-98

NAME

PRODUCT SPEC 108-1422

APPLICATION SPEC 114-11004

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

PLUG ASSEMBLY, .495[12.57] VERTICAL, .025[0.64] CENTER LINE, MICTOR

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A1 00779 767082

SCALE 8:1 SHEET 1 OF 1 REV E1