



main menue



- home
- test & measurement
- products
- skills
- download

online catalogue T&M

- clamp-type test probes
- crocodile clips
- test probes
- oscilloscope test probes
- measuring leads
- plugs
- sockets
 - 2 mm system
 - 2 mm safety system
 - 4 mm system
 - 4 mm safety system
- sets
- miscellaneous
- company
 - portrait
 - corporate association
 - location maps
 - fairs and exhibitions
 - jobs
 - imprint
 - terms and conditions

Home > sockets > sockets > PKI 10 A

PKI 10 A

datasheet for PKI 10 A
article number: 930103103



View Full-Size Image



search online catalogue

Search

Search

Messetermine

SPS/IPC/DRIVES
24. 11. 2015 - 26. 11. 2015

QR-Code



product description:		order number: 930 103-103	
description:		Pole terminal with claw edge and captive insulated head and insulated ring. 4 mm diameter nickel-plated brass threaded bolt with 2 mm diameter transverse hole. For insulated, non-rotating installation in equipment chassis and switchpanels with a wall thickness up to 2 mm.	
typ:		PKI 10 A gelb/yellow	
system:		4 mm system	
order number:		930 103-103	
color			
other color versions:			
technical data			
measurement category acc. to IEC 61010:		CAT I	
type of contact:		4 mm socket (unsprung), 2 mm cross hole	
type of termination:		M4 thread	
rated voltage:		30 VAC / 60 VDC	
rated current:		35 A	
Please consider derating curve!			
contact resistance:		2 mOhm	
mounting:		screw	
material			
contact material:		brass	
contact surface material:		nickel	
connecting nut material:		brass nickel - plated	
environmental conditions:			
temperature range:		-25 °C to +100 °C	
drawing			
			