

F00 & F01 Fixed Patch Panels - ST, FC Adapters

The fixed patch panel system in its basic form is supplied with the panels unloaded ready for you to install the adapter of your choice. The panel can also be pre-loaded complete with the required adapter and simple splice management kit, or pre-loaded with pigtails to meet your project needs.

F00



Unloaded F00XXX00

F01



Unloaded F01XXX00

Adapters



ST Singlemode

F00 (16 port)	With	F01 (24 port)	With
F00STS04	4 adapters	F01STS04	4 adapters
F00STS06	6 adapters	F01STS06	6 adapters
F00STS12	12 adapters	F01STS12	12 adapters
F00STS16	16 adapters	F01STS24	24 adapters

Adapter only part no. STUZR02

Adapters



FC Multimode

F00 (16 port)	With	F01 (24 port)	With
F00FCM04	4 adapters	F01FCM04	4 adapters
F00FCM06	6 adapters	F01FCM06	6 adapters
F00FCM12	12 adapters	F01FCM12	12 adapters
F00FCM16	16 adapters	F01FCM24	24 adapters

Adapter only part no. FCUPHBR-D

ST Multimode



F00 (16 port)	With	F01 (24 port)	With
F00STM04	4 adapters	F01STM04	4 adapters
F00STM06	6 adapters	F01STM06	6 adapters
F00STM12	12 adapters	F01STM12	12 adapters
F00STM16	16 adapters	F01STM24	24 adapters

Adapter only part no. STUPHBR

Adapters



FC Singlemode

F00 (16 port)	With	F01 (24 port)	With
F00FCS04	4 adapters	F01FCS04	4 adapters
F00FCS06	6 adapters	F01FCS06	6 adapters
F00FCS12	12 adapters	F01FCS12	12 adapters
F00FCS16	16 adapters	F01FCS24	24 adapters

Adapter only part no. FCUZR02-D

FCA Singlemode



F00 (16 port)	With	F01 (24 port)	With
F00FCA04	4 adapters	F01FCA04	4 adapters
F00FCA06	6 adapters	F01FCA06	6 adapters
F00FCA12	12 adapters	F01FCA12	12 adapters
F00FCA16	16 adapters	F01FCA24	24 adapters

Adapter only part no. FCAPCUZR02-D

Specification:

Dimensions Width: 19" - 483mm, Depth: 8" - 200mm, Height: 1u - 44mm, Weight: 2.6kg Fully loaded,
Cable entry 6 x 20mm gland holes Colour: Black

