



PART NUMBER		TAB SIZE	WIRE RANGE mm ²	DIMENSIONS mm		
PREFIX	PK			A ^{±.38}	B ^{±.25}	C ^{±.25}
DMNF2-63F1M	-C -M	6,3 X 0,8 (.250 X .032)	1,5-2,5 (16-14)	22,9 (.90)	10,41 (.41)	7,05 (.28)



NOTES:

1. USED FOR:
 - A. 600V MAX. VOLTAGE RATING.
 - B. 105° C (221°F) MAX. TEMP. RATING
 - C. STRANDED COPPER WIRE ONLY.
2. PACKAGE QTY:
 - A. STD: C=100
 - B. BULK: M=1000
3. MATERIAL:
 - A. STAMPING: CDA 260 BRASS, NICKEL PLATED
 - B. HOUSING: TYPE 6/6 NYLON TRANSLUCENT BLUE
4. WIRE STRIP LENGTH: 7,1 $^{+0.8}_{-0}$ (9/32 $^{+1/32}_{-0}$)
5. DIMENSIONS IN BRACKETS ARE IN INCHES OR AWG.
6. INSTALLATION TOOLS: REF. DWGS.
A41522, A41523, A41524, A41525



A41503_04

04	7/03	KLFU		ADDED INTERNAL SERRATIONS										
03	10/97	TM	WJB	CHANGED DECIMAL POINTS TO COMMAS	06432	LA	DH							
02	1/97	TM	RLS	UPDATE DIMENSIONS, WAS TIN PLATED FILESPEC WAS NPC-A41503-01	05478	LA	DH							
01	1/92	BK	RLS	CHANGED COMMAS TO PERIODS #6 WAS A41511, #1C ADDED COPPER	00765	LA	KRS							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY	JMV	CHK'D	SCALE	NONE	DRAWING NO./CAD FILENAME	A41503

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DMNF2-63FIM-L](#)