





NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.



* PANDUIT PART NO.	WEIGHT LBS/100 PCS. (g)
FCC-A	0.60 (274)



1. REMOVE PROTECTIVE LINER.
2. PLACE IN DESIRED LOCATION.
3. APPLY PRESSURE TO TOP CENTER OF MOUNT.

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
2. MAXIMUM FLAT CABLE STACKING HEIGHT IN CLIP IS .17(4.3).

ADHESIVE BACKING
PRESSURE SENSITIVE FOAM TAPE .040 (1.02)
THICK WITH RUBBER ADHESIVE AND PROTECTIVE
LINER. MOUNT IS DESIGNED TO SUPPORT .5 LB.
(227g) MAXIMUM WEIGHT ON A CLEAN, DRY,
SMOOTH, GREASE-FREE SURFACE.

CAD FILENAMES/LAYERS

GB0239BD_PB_FCCACLIP_03



CORP.

TINLEY PARK, ILLINOIS

FLAT CABLE CLIP (FCC-A)

[illegible]