

General Purpose AC-DC Toggle Switches

Quick Make and Break AC-DC Rated 6 Amps 125 VAC, 3 Amps 250 VAC
UL recognized and CSA certified 15/32" bushing 11/16" toggle.

Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0103	110-73	S.P.S.T ON-NONE-OFF	Solder	4.23	3.28	2.88	2.53
683-0104	110-S-73	S.P.S.T ON-NONE-OFF	Screw	5.68	4.41	3.87	3.39
683-0105	111-16-73	S.P.S.T ON-NONE-OFF	Wire	5.68	4.41	3.87	3.39
683-0106	2BB62-73	S.P.D.T ON-NONE-ON	Solder	5.34	4.14	3.63	3.19
683-0107	2BK62-73	D.P.S.T ON-NONE-OFF	Solder	7.68	5.96	5.23	4.58
683-0108	2BK65-73	D.P.S.T ON-NONE-OFF	Wire	10.16	7.87	6.91	6.06
683-0109	2BL62-73	D.P.D.T ON-NONE-ON	Solder	8.82	6.63	5.99	5.26


Heavy Duty AC-DC Toggle Switches

16 Amps, 125 VAC 8 Amps 250 VAC 1 HP 125-250 VAC


Stock No.	Mfr.'s Type	Switch Action	Terminals	EACH			
				1-24	25-99	100-499	500-999
683-0110	DK284-73	D.P.S.T.	Screw	8.21	6.36	5.58	4.90

20 Amps 125 VAC — 10 Amps 250 VAC — 1 1/2 H.P. 125-250 VAC

683-0111	EK204-73	D.P.S.T.	Screw	12.29	9.53	8.36	7.33
----------	----------	----------	-------	-------	------	------	------



5



Curvette Snap-In Switches

Slow-make and break action. 0.250 quick connect terminals. 16 amps 125 VAC — 10 amps 250 VAC, 10(4) amps — 250 VAC. UL recognized and CSA and VDE certified. Rated life 50 M cycles at rated load. Also features our unique Visi-Rocker two-color molded curved rocker for low cost "ON" indication.




Stock No.	Mfr.'s Type	Switch Action	Rocker Color	EACH			
				1-24	25-99	100-499	500-999
683-0112	RA911-RB-B-O-N	S.P.S.T ON-NONE-OFF	Black	1.15	.75	.66	.58
683-0113	RA911-VB-B-O-V	S.P.S.T ON-NONE-OFF	Visi-Rocker*	1.25	.82	.72	.63
683-0114	RA911-VB-B-I-V	S.P.D.T ON-NONE-OFF	Visi-Rocker* with on-off imprint	1.25	.82	.72	.63
683-0115	RB911-RB-B-O-N	S.P.D.T ON-NONE-ON	Black	1.34	.88	.77	.67
683-0116	RC911-RB-B-O-N	S.P.D.T ON-OFF-ON	Black	1.34	.88	.77	.67
683-0117	LRA911-RS-B/125	S.P.S.T ON-NONE-OFF Lighted	Red	1.52	1.00	.88	.77

*Curvette Visi-Rocker has a second color molded-in for attractive low cost "ON" indication.

SC High Inrush Curvette Snap-In Switches

Designed to handle current surges over 100 amps. UL recognized and CSA certified for 20 amps 125 VAC — 15 amps 250 VAC.

Stock No.	Mfr.'s Type	Switch Action	Rocker Color	EACH			
				1-24	25-99	100-499	500-999
683-5512	RSCA621-RB-B-O-N	S.P.S.T ON-NONE-OFF	Black	1.65	1.08	.95	.83
683-5511	RGSC621-RB-B-O-N	D.P.S.T ON-NONE-OFF	Black	2.41	1.57	1.38	1.21
683-1611	LRGSC611-RS-B-O/125N	D.P.S.T ON-NONE-OFF Lighted	Red	2.87	2.22	1.95	1.71



Miniature Curvette Snap-In Switches

These double insulated miniature switches offer self-cleaning wiping action. Contact system rated at 4 amps 250 VAC — 8 amps 125 VAC, 6(4) amps 250 VAC. UL recognized and CSA and VDE certified. Also features our unique Visi-Rocker two molded curved rocker for low cost "ON" indication.



Stock No.	Mfr.'s Type	Switch Action	Terminals	Rocker Color	EACH			
					1-24	25-99	100-499	500-999
683-2007	62115919-0-9-V*	D.P.S.T ON-NONE-OFF	Solder	Visi-Rocker	1.87	1.10	.97	.84
683-0121	62111421-0-0-N	S.P.D.T ON-NONE-ON	Solder	Black	1.50	.98	.86	.75
683-0122	62112421-0-0-N	D.P.D.T ON-NONE-ON	Solder	Black	1.90	1.24	1.09	.96
683-0123	62116316-0-0-N	S.P.S.T ON-NONE-OFF	Solder	Black	1.57	1.02	.89	.78
683-0124	62115929-0-0-V*	D.P.S.T ON-NONE-OFF	0.187 Tabs	Visi-Rocker	2.23	1.45	1.27	1.11
683-0125	62116919-0-9-V*	S.P.S.T ON-NONE-OFF	0.187 Tabs	Visi-Rocker with 0-1 Mtg.	1.37	.90	.79	.69

*Curvette Visi-Rocker has a second color molded-in for attractive low cost "ON" indication.

Heavy Duty Rocker Switches

These full-size rocker switches are designed for AC and low voltage DC applications. They include a slow make, slow break contact mechanism, nylon snap-in brackets and are available to resolve most insulation requirements. They are rated at 15 amps 125 VAC, 28 VDC, 10 amps 250 VAC 3/4 H.P. UL recognized and CSA certified.

Stock No.	Mfr.'s Type	Switch Action	Terminals	Rocker Color	EACH			
					1-24	25-99	100-499	500-999
683-0126	TIGA50-6S-BL-NBL	S.P.S.T ON-NONE-OFF	Solder	Black	4.73	3.67	3.22	2.82
683-0127	TIGK50-6S-BL-NBL	D.P.S.T ON-NONE-OFF	Solder	Black	6.40	4.96	4.35	3.81
683-0128	LTILA50-6S-BL-RC-NBL	S.P.S.T ON-NONE-OFF	Solder	Black with Red Light	5.96	4.61	4.04	3.55



Drip Dry Rocker Switches

We have modified the tippette switches above to provide front panel dust and moisture protection with built in seal feature. UL recognized and CSA certified.

Stock No.	Mfr.'s Type	Switch Action	Terminals	Rocker Color	EACH			
					1-24	25-99	100-499	500-999
683-0129	TIGA54-6S-BL-WBL	S.P.S.T ON-NONE-OFF	Screw	Black	5.76	4.47	3.92	3.44
683-0130	TIGK54-6S-BL-WBL	D.P.S.T ON-NONE-OFF	Screw	Black	7.90	6.12	5.37	4.71