


**EXCEPTIONALLY SOFT, HIGHLY COMPRESSIBLE GAP FILLER**

Tpli™ 200 is a premium gap filler. A unique blend of boron nitride and silicone produce the highest performing interface pad.

Tpli™ 200's exceptional combination of high thermal conductivity and compliancy generate unmatched thermal resistances in a gap filling interface material.

Tpli™ 200 absorbs shock and relieves stresses, thus minimizing potential damage to components. Tpli™ 200 is electrically insulating, stable from -45°C to 200°C, and meets UL 94 HB rating.

FEATURES AND BENEFITS

- Thermal performance leader
- 6 W/mK thermal conductivity
- Soft and compliant
- Available in thicknesses from
0.010" - 0.200" (0.25mm - 5.0mm)

APPLICATIONS

- Notebook computers
- Handheld portable electronics
- Micro heat pipe thermal solutions
- Micro processors, memory chips,
and graphic processors
- Automotive engine control modules
- Wireless communication hardware

global solutions: local support™

Americas: +1.800.843.4556

Europe: +49.8031.2460.0

Asia: +86.755.2714.1166

CLV-customerservice@lairdtech.com

www.lairdtech.com/thermal

	TPLI™ 210	TPLI™ 220	TPLI™ 240	TPLI™ 260	TPLI™ 2100	TEST METHOD
Construction & Composition	Reinforced boron nitride filled silicone elastomer	Boron nitride filled silicone elastomer	Boron nitride filled silicone elastomer	Boron nitride filled silicone elastomer	Boron nitride filled silicone elastomer	
Color	Rose	Blue	Yellow	Grey	Grey	Visual
Thickness	0.010" (0.25mm)	0.020" (0.51mm)	0.040" (1.02mm)	0.060" (1.52mm)	0.100" (2.54mm)	
Thickness Tolerance	± 0.001" (± 0.025mm)	± 0.002" (± 0.05mm)	± 0.003" (± 0.08mm)	± 0.004" (± 0.10mm)	± 0.007" (± 0.18mm)	
Density	1.44 g/cc	1.43 g/cc	1.43 g/cc	1.38 g/cc	1.36 g/cc	Helium Pycnometer
Hardness	75 Shore OO	70 Shore OO	70 Shore OO	70 Shore OO	70 Shore OO	ASTM D2240
Tensile Strength	N/A	35 psi	35 psi	20 psi	15 psi	ASTM D412
% Elongation	N/A	5	5	5	5	ASTM D412
Outgassing TML (Post Cured)	0.08%	0.07%	0.07%	0.10%	0.15%	ASTM E595
Outgassing CVCN (Post Cured)	0.03%	0.02%	0.02%	0.04%	0.07%	ASTM E595
UL Flammability Rating	94 HB	94 HB	94 HB	94 HB	94 HB	E180840
Temperature Range	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	-45°C to 200°C	
Thermal Conductivity	6 W/mK	6 W/mK	6 W/mK	6 W/mK	6 W/mK	ASTM D5470 (modified)
Thermal Impedance @ 20 psi @ 138KPa	0.16°C - in²/W 1.03°C - cm²/W	0.21°C - in²/W 1.35°C - cm²/W	0.37°C - in²/W 2.45°C - cm²/W	0.49°C - in²/W 3.35°C - cm²/W	0.84°C - in²/W 5.81°C - cm²/W	ASTM D5470 (modified)
Thermal Expansion	51 ppm/C	123 ppm/C	72 ppm/C	72 ppm/C	96 ppm/C	IPC-TM-650 2.4.24
Breakdown Voltage	1,000 Volts AC	4,000 Volts AC	>5,000 Volts AC	>5,000 Volts AC	>5,000 Volts AC	ASTM D149
Volume Resistivity	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	5 x 10 ¹³ ohm-cm	ASTM D257
Dielectric Constant @ 1MHz	3.21	3.21	3.26	3.26	3.4	ASTM D150

STANDARD THICKNESSES

0.010" (0.25mm)	0.015" (0.38mm)	0.020" (0.51mm)	0.025" (0.64mm)
0.030" (0.76mm)	0.040" (1.02mm)	0.050" (1.27mm)	0.060" (1.52mm)
0.070" (1.78mm)	0.080" (2.03mm)	0.090" (2.29mm)	0.100" (2.54mm)
0.110" (2.79mm)	0.120" (3.05mm)	0.130" (3.30mm)	0.140" (3.56mm)
0.150" (3.81mm)	0.160" (4.06mm)	0.170" (4.32mm)	0.180" (4.57mm)
0.190" (4.83mm)	0.200" (5.08mm)	Consult the factory for alternate thicknesses.	

STANDARD SHEET SIZES

8" x 8" (203mm x 203 mm) & 16" x 16" (406mm x 406mm). Tpli™ 200 may be die cut into individual shapes.

PRESSURE SENSITIVE ADHESIVE

Request no adhesive with "AO" suffix. Request adhesive on one side with "A1" suffix. Double sided adhesive is not available

REINFORCEMENT

Fiberglass is required in thicknesses of 0.010" (0.25mm) and 0.015" (0.38mm). Reinforcement is optional in thicknesses 0.020" (0.5mm) and 0.025" (0.63mm). Indicate fiberglass by "FG" suffix. Thicknesses above 0.025" (0.63mm) are not reinforced.

Data for design engineer guidance only. Observed performance varies in application. Engineers are reminded to test the material in application.

THR-DS-Tpli-200 0710

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2010 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trademarks or registered trademarks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.

A13519-00 Rev G, 2/05/07

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Laird Technologies:

[A10092-63](#) [A10092-45](#) [A10092-02](#) [A10092-01](#) [A10102-02](#) [A10102-01](#) [A10103-07](#) [A10103-01](#) [A10103-02](#)
[A10104-02](#) [A10104-01](#) [A10105-02](#) [A10105-01](#) [A10106-01](#) [A10106-02](#) [A10263-13](#) [A10263-08](#) [A10263-01](#) [A10263-02](#) [A10107-01](#) [A10107-02](#) [A10108-01](#) [A10108-02](#) [A10109-01](#) [A10110-01](#) [A10110-02](#) [A10111-02](#) [A10111-01](#)
[A10093-41](#) [A10080-39](#) [A10093-37](#) [A10080-02](#) [A10080-01](#) [A10093-01](#) [A10112-02](#) [A10112-01](#) [A10095-11](#) [A10095-13](#) [A10095-02](#) [A10095-01](#) [A10096-67](#) [A10096-79](#) [A10222-11](#) [A10096-35](#) [A10222-02](#) [A10096-01](#) [A10096-02](#)
[A10097-18](#) [A10097-01](#) [A10098-12](#) [A10098-32](#) [A10098-01](#) [A10098-02](#) [A10099-18](#) [A10099-16](#) [A10099-01](#) [A10099-02](#) [A10100-14](#) [A10100-23](#) [A10100-01](#) [A10100-02](#) [A10101-09](#) [A10101-01](#) [A10101-02](#) [A10093-02](#) [A10092-122](#)
[A10265-02](#) [A10264-14](#) [A10101-04](#) [A10109-02](#) [A10264-01](#) [A10097-02](#) [A10264-06](#) [A10097-20](#) [A10080-109](#)
[A10092-155](#) [A10264-09](#)