



Omnimate Range - 5.00 mm Pitch



Pin headers SL-SMT 5.00/180



D = up to 8 poles $\varnothing 1.4^{+0.1}$
from 9 poles $\varnothing 1.5^{+0.1}$

Technical Data		VDE	UL	CSA
Rated voltage	V	250*	300	300
Rated current	A	15	15	15

*Overvoltage category III / Pollution severity 3
Additional technical data see page 2

Solder pin length 1.5 mm
Tape-on-Reel 
Color: Black
Tape width 56 mm


Poles	Type	Part No.	Qty.
2	SL-SMT 5.00/2/180	1797800000	200
3	SL-SMT 5.00/3/180	1797810000	200
4	SL-SMT 5.00/4/180	1797820000	200
5	SL-SMT 5.00/5/180	1797830000	200
6	SL-SMT 5.00/6/180	1797840000	200
7	SL-SMT 5.00/7/180	1797850000	200
8	SL-SMT 5.00/8/180	1797860000	200

Additional pole numbers and tape widths on request.
Minimum order quantities may apply.

Accessories see PCB Products Selection Guide	Page
Fixing	-
Marking	190
Coding	192,193
Miscellaneous	-



Pin headers SL-SMT 5.00/180G



D = up to 8 poles $\varnothing 1.4^{+0.1}$
from 9 poles $\varnothing 1.5^{+0.1}$

Technical Data		VDE	UL	CSA
Rated voltage	V	250*	300	300
Rated current	A	15	15	15

*Overvoltage category III / Pollution severity 3
Additional technical data see page 2

Solder pin length 1.5 mm
Tape-on-Reel 
Color: Black
Tape width 56 mm

Poles	Type	Part No.	Qty.
2	SL-SMT 5.00/2/180G	1797870000	200
3	SL-SMT 5.00/3/180G	1797880000	200
4	SL-SMT 5.00/4/180G	1797890000	200
5	SL-SMT 5.00/5/180G	1797900000	200
6	SL-SMT 5.00/6/180G	1797910000	200
7	SL-SMT 5.00/7/180G	1797920000	200

Additional pole numbers and tape widths on request.
Minimum order quantities may apply.

Accessories see PCB Products Selection Guide	Page
Fixing	-
Marking	190
Coding	192,193
Miscellaneous	-