



| LOC | DIST | REVISIONS |     |                           |         |      |
|-----|------|-----------|-----|---------------------------|---------|------|
| G   | 14   | P         | LTR | DESCRIPTION               | DATE    | OWN  |
|     |      |           |     |                           |         | APVD |
|     |      |           | C3  | REVISED PER ECO-12-005490 | 21MAR12 | KH   |



AMP  
WIRE RANGE

8 AWG  
SOLID OR STRANDED

- 1 STAMP AMP 8 APPROX AS SHOWN
- 2 NICKEL PER ASTM B-162, ANNEALED
- 3 WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL



328822

PART NO.

|                                                                         |                                        |                                        |                                                                                                                                |            |               |           |
|-------------------------------------------------------------------------|----------------------------------------|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|------------|---------------|-----------|
| MAX RECOMMENDED OPERATING TEMPERATURE:<br>649°C MAX                     | THIS DRAWING IS A CONTROLLED DOCUMENT. | DWN<br>TA BRINKMAN<br>3-24-93          | <div>TE Connectivity</div> <div>TE CONNECTIVITY</div> <div>TERMINAL, RING TONGUE,<br/>HIGH TEMPERATURE,<br/>STRATO-THERM</div> |            |               |           |
|                                                                         |                                        | CHK<br>DA PATTERSON<br>3-24-93         |                                                                                                                                |            |               |           |
|                                                                         |                                        | APVD<br>JL MECKLEY<br>3-24-93          |                                                                                                                                |            |               |           |
| VOLTAGE RATING:<br>N/A                                                  | DIMENSIONS:<br>mm[INCHES]              | TOLERANCES UNLESS OTHERWISE SPECIFIED: | PRODUCT SPEC                                                                                                                   | NAME       | SIZE          | CAGE CODE |
| CIRCULAR MIL AREA:<br>6.64-10.5mm² [13,100-20,800]<br>SOLID OR STRANDED |                                        |                                        | APPLICATION SPEC                                                                                                               | DRAWING NO | RESTRICTED TO |           |
|                                                                         |                                        |                                        | WEIGHT                                                                                                                         | A200779    | C-328822      |           |
|                                                                         |                                        |                                        | CUSTOMER DRAWING                                                                                                               | SCALE 8:1  | SHEET 1 OF 1  | REV C3    |