

Low shrink temperature polyolefin heat-shrinkable tubing.

Rapid recovery at low temperatures, can be used with temperature sensitive materials, 2:1 shrink ratio, excellent physical and electrical performance.

LSTT is a highly flexible, low shrink temperature heat-shrinkable tubing. Easy to handle and install, its low shrink temperature offers exceptionally fast recovery for maximum efficiency in high volume commercial applications and makes


it suitable for use on or near delicate temperature sensitive materials eg. PVC jacketed wire and cable. The material contains no known halogens. Although not flame retarded, LSTT meets the automotive flame propagation standard MVSS 302.

LSTT gives good physical and electrical performance. Typical applications are electrical termination insulation, color coding, covering of heat sensitive devices, cosmetic coverings and mechanical protection.

Temperature rating

Operating temperature range:	-40°C to +125°C
Minimum shrink temperature:	+65°C
Minimum full recovery temperature:	+110°C

Ordering information



Inside diameter		Wall thickness	Standard package	
D (min)	d (max)	W (nom)	Spool quantity	Ordering description
Expanded as supplied	Recovered after heating	Recovered after heating		
mm	mm	mm	m	
1.6	0.8	0.50	300	LSTT-1.6-color code
2.4	1.2	0.55	150	LSTT-2.4-color code
3.2	1.6	0.55	150	LSTT-3.2-color code
4.8	2.4	0.55	150	LSTT-4.8-color code
6.4	3.2	0.65	75	LSTT-6.4-color code
9.5	4.8	0.65	75	LSTT-9.5-color code
12.7	6.4	0.65	75	LSTT-12.7-color code
19.0	9.5	0.80	75	LSTT-19-color code
25.4	12.7	0.95	30	LSTT-25.4-color code
32.0	16.0	1.05	30	LSTT-32-color code
38.0	19.0	1.05	30	LSTT-38-color code
52.0	26.0	1.30	30	LSTT-52 available in black only

Standard colors

Standard color	Black	Red	Yellow	Blue	White
Code	0	2	4	6	9
Non Standard color	Green	Grey	Clear		
Code	5	8	X		

Performance

Test	Test method	Test requirement
Heat Ageing:	ISO 188 (168h at 125°C)	Tensile strength: 15 MPa (min) Ultimate elongation: 300% (min)
Corrosion resistance:	ASTM D2671 (16h at 150°C)	No corrosion of mirrors
Flame retardancy:	MVSS 302	100 mm/min (max)
Fluid resistance:	24 h at 23°C, ISO 37 Ultimate elongation	Tensile strength: 15 MPa (min) 200% (min) Hydraulic fluid (J1703) Battery acid Anti freeze

For full product performance details consult Raychem Specification RW 2051.

To ensure dimensional stability, LSTT should be stored at temperatures not exceeding 40°C.

Specifications

Raychem specification RW 2051.

Material Safety Data Sheet available on request.

Installation instructions available on request.

Raychem and LSTT are trademarks of Raychem Interconnect, a division of Tyco Electronics Corporation.

Users should independently evaluate the suitability of the product for their application.

Tyco Electronics Corporation	Tyco Electronics UK Ltd.	Tyco Electronics Raychem K.K.	Tyco Electronics Singapore Pte Ltd.
300 Constitution Drive Menlo Park, CA 94025-1164 USA Tel: (800) 926-2425 (US & Canada) Tel: +1 (650) 361-3860 (All other countries)	Faraday Road Dorcan, Swindon, SN3 5HH United Kingdom Tel: +44 1793 528171	3816 Noborito, Tama-ku Kawasaki, Kanagawa 214-8533 Japan Tel: +81 44 900 5102	Asia Pacific Headquarters 26 Ang Mo Kio, Industrial Park 2 Singapore 569507 Tel: +65 4866 151

All information, including illustrations, is believed to be reliable. Users, however, should independently evaluate the suitability of each product for their application. Tyco Electronics Corporation makes no warranties as to the accuracy or completeness of the information, and disclaims any liability regarding its use. Tyco Electronics Corporation's only obligations are those in the Standard Terms and Conditions of Sale for these products and in no case will Tyco Electronics Corporation be liable for any incidental, indirect, or consequential damages arising from the sale, resale, use, or misuse of the product. Tyco Electronics Corporation's Specifications are subject to change without notice. In addition, Tyco Electronics Corporation reserves the right to make changes in materials or processing without notification to the Buyer which do not affect compliance with any applicable specification.

For more information about this product visit www.tycoelectronics.com and www.raychem.com