



S50394T1.DGN



I. APPLICABLE HOUSING : 51110-***1
: 51110-***5*



ENG.No.

B	VOID PART NO. PER	---	ANG	LING	040223	MATERIAL :		 MOLEX SINGAPORE PTE LTD SHEET 1 OF 1	
A2	ECN S2004-0719	---	NASH	LING	02/07/12	PHOSPHOR BRONZE (THK=0.152)			
A1	ADD GOLD FLASH AS PER	---	SEE	LING	980312	FINISH :		GENERAL TOLERANCES ± 0.20/0.005	
	ECN*S2003-0030					SEE NOTES		REV B	
	ADD 0.38 Pd/Ni WITH GOLD							DWG. NO.:	
	FLASH AS PER PDR*98-01-							SD150394-8***	
	0267 (ECN*SI998-0364)							TITLE :	
A	REL AS PER ECN*	S40519	50	EDP	940420			2.0mm GRID W TO B	
LTR	REVISION RECORD	ECN	DR	CHK	DATE	DRAWN BY S.O.	940420	CHK'D BY EDPOH	940427
REVISE ONLY ON CAD SYSTEM						APPR'D BY ROY	940428	SCALE 1:5.1	CONN. CRIMP TERMINAL


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX (S) PTE LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

10 9 8 7 6 5 4 3 2 1


ENG. NO.		Au. PLATE THICKNESS (μ m MIN.)
FORM: LOOSE	FORM: CHAIN	
50394-8100	50394-8051	0.38
50394-8200	50394-8052	0.76
50394-8400	50394-8054	GOLD FLASH 0.05-0.125 μ m



B-B




A-A




NOTES :

1. APPLICABLE HOUSING : 51110-***1
: 51110-**5*

WINDING DIRECTION



VIEW Z



VIEW Z

ADD WINDING DIRECTION EC NO: S2014-0327 DRWN:ATSEE CHKD:FANNYWONG APPR:LBLEE REV B1	DESCRIPTION 2013/09/30 2013/09/30 2013/11/13	QUALITY SYMBOLS F A =0 F G =0 F P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE NTS	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY S.Q	DATE 1994/04/20	TITLE SALES DRAWING 2.0MM GRID W TO B CONN. CRIMP TERMINAL molex SD-50394-8XXX			
			4 PLACES	± ---	± ---	CHECKED BY EDPOH	DATE 1994/04/27				
			3 PLACES	± ---	± ---	APPROVED BY BBYEE	DATE 2013/04/28				
			2 PLACES	± 0.20	± ---	MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
			1 PLACE	± ---	± ---	SEE TABLE		SD-50394-8XXX		1 OF 1	
			0 PLACE	± ---	± ---	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					
			ANGULAR ± 3 °		SIZE A3						
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS											

9 8 7 6 5 4 3 2 1