

**Sura Magnets AB**  
Hamragatan 2  
S-614 31 Söderköping  
Sverige/Sweden

Telefon +46 (0) 121 353 10  
Fax +46 (0) 121 353 15  
E-mail [info@suramagnets.se](mailto:info@suramagnets.se)  
Internet [www.suramagnets.se](http://www.suramagnets.se)




# Partnumber: NA35-9-015-1

Material : Neodym 35

Dimensions

| D     | H    | d1      | d2     | kraft |
|-------|------|---------|--------|-------|
| 15 mm | 4 mm | 10,7 mm | 5,3 mm | 40 N  |

Magnetisation: Axially magnetized



| Grade | Remanence<br>( T ) |      | Coercivity BHc<br>( kA/m ) |       | Coercivity Ihc<br>( kA/m ) | Energi product<br>BH max ( kJ/m3 ) |       | Max Work<br>temp |
|-------|--------------------|------|----------------------------|-------|----------------------------|------------------------------------|-------|------------------|
|       | Min                | Typ  | Min                        | Typ   |                            | Min                                | Typ   |                  |
| N35   | 1,17               | 1,21 | 860                        | 915,4 | >=955                      | 262,7                              | 278,6 | <=80°            |