





	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--

Male



Cover

- Product Specification
- Material
- Insulator : Glass-Filled Thermoplastic PBT, UL94V-0,Black
- Contact : Copper alloy, plating gold flash selective gold
- Shell : Steel, 1000µ" Tin Over 500µ" min Copper
- Electrical
- Contact Resistance : 20 milliohms Max at 1 AMP DC.
- Insulation Resistance : 1000 megohms at 500 VDC
- Dielectric Withstanding Voltage : 1000 VAC/rms 60Hz for 1 minute
- Current Rating : 3 AMP
- Voltage Rating : 250 VAC/rms 60Hz
- Wire Spec : 26 AWG-28 AWG
- Operating Temperature:-20°C--+85°C
- ⑤ UL E No #E198287


Order Code:

A-DXF xx LP III/Z

Contact style: F - Female S - Male

No. of Contacts 09 / 15 / 25 / 37

Standard Quality class III



Strain Relief

Without Insulator Support

Dimensions	Positions	A	B	C	E	F
	9	30.81	24.99	16.92	11.08	13.10
	15	39.20	33.30	25.25	19.39	20.70
	25	53.04	47.04	38.96	33.24	33.68
	37	69.40	63.50	55.42	49.86	50.30

RoHS compliant

Unit:mm

G	RoHS compliant										
	Unit:mm										
	Scale	Free	⑤	Correct the UL-File number			03.04.2014	Winnie			Customer-No.
	TOLERANCE		④	Update 17.58&17.28 into 17.40&17.10mm			07.03.2014	Winnie	Drawn	15.08.2012	Lucas
	X.	±0.38	④								
	X.X	±0.25	③	Update the wire specification			28.06.2013	Winnie	Approved	03.04.2014	Winnie
	X.XX	±0.13	②	Add the wire specification			06.03.2013	Winnie			
	DIM	TOL	①	Add the UL file No.			18.10.2012	Winnie			
	X.°	±3°	①								
	X.X°	±1.0°	①	Drawn			15.08.2012	Lucas			
H	Angle	TOL	Id.	Modification			Date	Name	Replace		
Drawing-No.											
ASS 4891 CO											
rev05											
Sheet 1/2											
H											



