

SERIES COM1

FEATURES


- ULTRA SMALL PACKAGE OF 3.2 x 2.5 x 1.0mm TYPICAL
- LOW SUPPLY VOLTAGE OF 1.8 AND 2.5 VDC AVAILABLE
- STANDBY FUNCTION
- LEAD FREE / RoHS COMPLIANT

SPECIFICATIONS

SERIES		COM118	COM125	COM13
FREQUENCY RANGE		1.544 MHz TO 60.000 MHz		
FREQUENCY STABILITY **		COM11810 : ±100 ppm	COM12510 : ±100 ppm	COM1310 : ±100ppm
		COM11805 : ±50 ppm	COM12505 : ±50 ppm	COM1305 : ±50ppm
		COM118025 : ±25 ppm	COM125025 : ±25 ppm	COM13025 : ±25ppm
OPERATING TEMPERATURE RANGE		-10°C TO +70°C (-40°C TO +85°C AVAILABLE)		
STORAGE TEMPERATURE RANGE		-55° C TO +125° C		
INPUT	VOLTAGE	+1.8 VDC ±5%	+2.5 VDC ±5%	+3.3 VDC ±10%
	CURRENT (MAX)	1.544 MHz TO 9.99MHz: 5 mA MAX 10.00 MHz TO 31.99 MHz: 6 mA MAX 32.00 MHz TO 60.00 MHz: 15mA MAX	1.544 MHz TO 9.99MHz: 6 mA MAX 10.00 MHz TO 31.99 MHz: 8 mA MAX 32.00 MHz TO 60.00 MHz: 20mA MAX	1.544 MHz TO 9.99MHz: 7 mA MAX 10.00 MHz TO 31.99 MHz: 10 mA MAX 32.00 MHz TO 60.00 MHz: 20mA MAX
	SYMMETRY	40 TO 60% AT 50% VDD (45 TO 55% AVAILABLE)		
OUTPUT	RISE / FALL TIME	5 ns MAX		20 ns MAX
	LOGIC "0" LEVEL	VCC X 0.1 V MAX		
	LOGIC "1" LEVEL	VCC X 0.9 V MIN		
	LOAD	15 pF (HCMOS)		
ENABLE/DISABLE FUNCTION		PIN 1: HIGH OR OPEN PIN 3: OSCILLATION PIN 1: LOW PIN 3: HIGH IMPEDANCE		
START UP TIME		10 ms MAX		
STANDBY CURRENT		10 µA MAX		

** INCLUSIVE OF 25°C TOLERANCE, OPERATING TEMPERATURE RANGE, VOLTAGE OR LOAD CHANGES, AGING, SHOCK AND VIBRATION. CONSULT FACTORY FOR TIGHTER STABILITY OPTIONS.

OUTLINE DRAWING



PACKAGING


178 mm REEL DIAMETER, 8mm TAPE WIDTH, 4mm PITCH
QUANTITY: 1000 PIECES PER REEL

PART NUMBERING SYSTEM

SERIES	SUPPLY VOLTAGE	FREQUENCY STABILITY	FREQUENCY	EXTENDED TEMPERATURE	DUTY CYCLE	TAPE & REEL
COM1	18 1.8V 25 2.5V 3 3.3V	10 ± 100 PPM 05 ± 50 PPM 025 ± 25 PPM	IN MHZ	EXT	T 45% TO 55%	TR

EXAMPLES: COM1305-25.000-EXT-T-TR

REFLOW SOLDERING PROFILE



CARRIER TAPE DIMENSIONS

