


REV.	DATE	ECR NO.	DESCRIPTION
NC	04/10/07	—	INITIAL RELEASE
A	08/19/08	100047	ADD "50 ohms" TO PART DESCRIPTION



				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
8					DRAWN	GRS	08/19/08						
7					CHECKED								
6					ISSUED			PART DESCRIPTION BNC JACK TO SMB PLUG ADAPTER – 50 ohms					
5					SHEET	1 OF 1							
4	CONTACT PIN	BER. COPPER	GOLD		1			PART NO. 242185					
3	INSULATOR	PTFE	NATURAL		1								
2	SMB BODY	BRASS	GOLD		1			DWG. NO. 242185.DWG REV. A SIZE A SCALE NA					
1	BNC BODY	BRASS	NICKEL	1									
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/242/242185.DWG								